

## Eaton 630NHG2B-400

Fuse-link, LV, 630 A, AC 400 V, NH2, gL/gG, IEC, dual indicator, live gripping lugs

PRODUCT NAME	Eaton Bussmann series low voltage NH Fuse
CATALOG NUMBER	630NHG2B-400
PRODUCT LENGTH/DEPTH	150 mm
PRODUCT HEIGHT	71 mm
PRODUCT WIDTH	54 mm
PRODUCT WEIGHT	659 g
COMPLIANCES	RoHS Compliant CE Marked
CERTIFICATIONS	IEC 60269-1 IEC 60269-2 DIN 43620

<b>AMPERAGE RATING</b>	630 A
<b>FITTED WITH:</b>	Metal gripping lugs
<b>FUSE SIZE</b>	NH2
<b>CURRENT TYPE</b>	AC
<b>BREAKING CAPACITY</b>	120 kA
<b>FREQUENCY RATING - MAX</b>	62 Hz
<b>FREQUENCY RATING - MIN</b>	45 Hz
<b>RATED SWITCHING CAPACITY</b>	120 kA
<b>RATED VOLTAGE AC</b>	400 V
<b>CLASS</b>	Class gG/gL
<b>FUSE TYPE</b>	Square body with knife blade contact
<b>ACCESSORY/SPARE PART TYPE</b>	SDL-2 Solid link FEH- Fuse extraction handle SD12-SK Shroud kit SD12-PB 2-phase barriers and 2 ganging links TD2-IP20 Triple pole protection kit
<b>UTILIZATION CATEGORY</b>	gL/gG (cable protection/equipment protection)
<b>INTERRUPT RATING</b>	120 kAIC
<b>FUSE INDICATOR</b>	Combination fuse status indicator
<b>INSULATED METAL GRIPPING LUGS (IMGL)</b>	No
<b>WATT LOSSES</b>	44 W
<b>CONNECTION</b>	Blade end
<b>CONSTRUCTION</b>	NH2
<b>CONSTRUCTION SIZE</b>	NH2
<b>FUSE SHAPE</b>	Knife blade contacts Square body
<b>VOLTAGE TYPE</b>	AC
<b>SUITABLE FOR</b>	SD2-D Single pole NH Fuse base Microswitch 170H0235 Microswitch 170H0236 EBH Size 00 to 4 Horizontal fuse switch-disconnectors TD2-D Triple pole NH Fuse

## DECLARATIONS OF CONFORMITY

[eaton-low-voltage-nh-fuse-declaration-of-conformity-uk250967en.pdf](#)

	base
MATERIAL	Ceramic body
QUANTITY	3
VOLTAGE RATING	400 V
TYPE	Fuse
APPLICATION	<ul style="list-style-type: none"><li>• industrial</li><li>• Utilities, Solar, Wind</li></ul>
RATED SWITCHING CAPACITY AC	120 kA

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

