

Eaton 630NHG3BI-400

Eaton Bussmann series low voltage NH Fuse, 400V, 630A, 120 kAIC, Combination fuse status indicator, fuse, Class C gL/gG

PRODUCT NAME	Eaton Bussmann series low voltage NH Fuse
CATALOG NUMBER	630NHG3BI-400
UPC	051712233552
PRODUCT LENGTH/DEPTH	150 mm
PRODUCT HEIGHT	86 mm
PRODUCT WIDTH	71 mm
PRODUCT WEIGHT	1140 g
COMPLIANCES	RoHS Compliant CE Marked
CERTIFICATIONS	IEC 60269-1 IEC 60269-2 DIN 43620

AMPERAGE RATING	630 A
FITTED WITH:	Insulated metal gripping lugs
FUSE SIZE	NH3
CURRENT TYPE	AC
BREAKING CAPACITY	120 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
RATED SWITCHING CAPACITY	120 kA
RATED VOLTAGE AC	400 V
CLASS	Class gG/gL
FUSE TYPE	Square body with knife blade contact
ACCESSORY/SPARE PART TYPE	SDL-3 Solid link FEH- Fuse extraction handle SD3-SK Shroud kit SD3-PB 2-phase barriers and 2 ganging links TD3-IP20 Triple pole protection kit
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
INTERRUPT RATING	120 kAIC
FUSE INDICATOR	Combination fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	Yes
WATT LOSSES	36 W
CONNECTION	Blade end
CONSTRUCTION	NH3
CONSTRUCTION SIZE	NH3
FUSE SHAPE	Knife blade contacts Square body
VOLTAGE TYPE	AC
SUITABLE FOR	SD3-D Single pole NH Fuse base Microswitch 170H0235 EBH Size 00 to 4 Horizontal fuse switch-disconnectors TD3-D Triple pole NH Fuse

	base
MATERIAL	Ceramic body
PACKAGING TYPE	Standard
QUANTITY	3
VOLTAGE RATING	400 V
TYPE	Fuse
APPLICATION	• industrial • Utilities, Solar, Wind
RATED SWITCHING CAPACITY AC	120 kA

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

