

Eaton 63NHG000B-690

Fuse-link, LV, 63 A, AC 690 V, NH000, gL/gG, IEC, dual indicator, live gripping lugs

PRODUCT NAME	Eaton Bussmann series low voltage NH Fuse
CATALOG NUMBER	63NHG000B-690
UPC	051712683753
PRODUCT LENGTH/DEPTH	79 mm
PRODUCT HEIGHT	51 mm
PRODUCT WIDTH	21 mm
PRODUCT WEIGHT	151.333 g
COMPLIANCES	CE CE Marked RoHS Compliant
CERTIFICATIONS	IEC 60269-1 IEC 60269-2 DIN 43620

AMPERAGE RATING	63 A
FITTED WITH:	Metal gripping lugs
FUSE SIZE	NH000
CURRENT TYPE	AC
BREAKING CAPACITY	120 kA
RATED SWITCHING CAPACITY	120 kA
RATED VOLTAGE AC	690 V
CLASS	Class gG/gL
FUSE TYPE	Square body with knife blade contact
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
INTERRUPT RATING	120 kAIC
FUSE INDICATOR	Combination fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
CONNECTION	Blade end
CONSTRUCTION	NH000
CONSTRUCTION SIZE	NH000
FUSE SHAPE	Square body Knife blade contacts
VOLTAGE TYPE	AC
SUITABLE FOR	Microswitch 170H0236 EBF Vertical fuse rail EBV Vertical fuse switch-disconnectors EBH Size 000 Horizontal fuse switch-disconnectors
MATERIAL	Ceramic body
QUANTITY	3
VOLTAGE RATING	690 V
TYPE	Fuse
APPLICATION	• industrial • Utilities, Solar, Wind
RATED SWITCHING CAPACITY AC	120 kA



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

