



Eaton 654019FULL-0135X

Eaton, Alarms & signalling devices, Fulleon, Symphoni G1 Euro sounder, Weatherproof, Red housing, VdS approved (SY/WP/R/E SLOW WHOOP)

□□□□

PRODUCT NAME	Eaton Symphoni Fire alarm sounder
CATALOG NUMBER	654019FULL-0135X
PRODUCT LENGTH/DEPTH	96 mm
PRODUCT HEIGHT	110 mm
PRODUCT WIDTH	110 mm
PRODUCT WEIGHT	0.32 kg
CERTIFICATIONS	Not Applicable

□□□□

NUMBER OF TONES	3
COLOR HOUSING	Red
MATERIAL HOUSING	Plastic
SOUND OUTPUT	100 dB
NOMINAL VOLTAGE	24 V
TYPE OF CURRENT	DC
ELECTRICITY CONSUMPTION	0.005 A
ADDRESSING MODE	Hard addressing
ALARM CURRENT	5 mA
CONSTRUCTION MATERIAL	ABS/FR
EN CERTIFIED TONES	3
OPERATING TEMPERATURE - MAX	70 °C
OPERATING TEMPERATURE - MIN	-25 °C
STANDBY CURRENT	0
SYSTEM TOPOLOGY	Conventional (Non-Addressable)
TONES	3
VOICE TONES	No
PRODUCT BRANDING	Eaton
HUMIDITY (NON CONDENSING) - MAX	95 %
HUMIDITY (NON CONDENSING) - MIN	0 %
DEGREE OF PROTECTION	IP66
EN CERTIFICATION STANDARDS	EN54 Pt3 (Fire Alarm Sounders)
CABLE ENTRY	M20 hole
SYSTEM WIRING	0.28 - 2.5 mm

□□

