



## Eaton 680007FULL-0008

Eaton, Alarms & signalling devices, Fulleon, Symphoni Voice Plus sounder beacon, Weatherproof, Red lens, Red flash, Red housing, Set to tone 7, Voice message set VP001ASY, Set to Tone 7



<b>PRODUCT NAME</b>	Eaton Symphoni Fire alarm sounder
<b>CATALOG NUMBER</b>	680007FULL-0008
<b>PRODUCT LENGTH/DEPTH</b>	100 mm
<b>PRODUCT HEIGHT</b>	110 mm
<b>PRODUCT WIDTH</b>	110 mm
<b>PRODUCT WEIGHT</b>	0.32 kg
<b>COMPLIANCES</b>	EN



Powering Business Worldwide

□□□□

□□

<b>NOMINAL VOLTAGE - MAX</b>	60 V
<b>NOMINAL VOLTAGE - MIN</b>	9 V
<b>TYPE OF CURRENT</b>	DC
<b>ELECTRICITY CONSUMPTION</b>	0.012 A
<b>POWER</b>	0.3 W
<b>LENS COLOR</b>	Red
<b>LAMP TYPE</b>	LED
<b>SOUND OUTPUT</b>	100 dB
<b>TYPE OF OPTICAL SIGNAL</b>	Flash light
<b>TYPE OF ACOUSTIC SIGNAL DEVICE</b>	Siren
<b>TYPE OF ACOUSTIC SIGNAL</b>	Pulse tone/continuous tone
<b>MOUNTING METHOD</b>	Surface mounting
<b>COLOR HOUSING</b>	Red
<b>FREQUENCY SOUND SIGNAL - MAX</b>	1.2 Kilo Hertz
<b>FREQUENCY SOUND SIGNAL - MIN</b>	0.5 Kilo Hertz
<b>ALARM CURRENT - MAX</b>	12 mA
<b>ALARM CURRENT - MIN</b>	8 mA
<b>CONSTRUCTION MATERIAL</b>	ABS/FR
<b>EN CERTIFIED TONES</b>	7
<b>HUMIDITY (NON CONDENSING) - MAX</b>	95 %
<b>HUMIDITY (NON CONDENSING) - MIN</b>	0 %
<b>OPERATING TEMPERATURE - MAX</b>	70 °C
<b>OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>SYSTEM TYPOLOGY</b>	Conventional (Non-addressable)
<b>TONES</b>	7
<b>VOICE TONES</b>	Yes
<b>DEGREE OF PROTECTION</b>	IP66
<b>SUITABLE FOR</b>	Ceiling Mounting Wall Mounting
<b>CABLE ENTRY</b>	M20 hole
<b>LIGHT COLOR</b>	Red
<b>EN CERTIFICATION</b>	EN54 Pt3 (Fire Alarm)

