



□□□□

## Eaton 7.2ADFHO31.5

Air fuse-link, medium voltage, 31.5 A, AC 7.2 kV, 336 x 50.8 mm, back-up, BS, with striker

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series medium voltage BS air fuse
<b>CATALOG NUMBER</b>	7.2ADFHO31.5
<b>PRODUCT LENGTH/DEPTH</b>	254 mm
<b>PRODUCT HEIGHT</b>	50.8 mm
<b>PRODUCT WIDTH</b>	50.8 mm
<b>PRODUCT WEIGHT</b>	1500 g
<b>COMPLIANCES</b>	BS 2692-1



Powering Business Worldwide

<b>USED WITH</b>	A3354710 Fuse clip
<b>AMPERAGE RATING</b>	31.5 A
<b>FUSE INDICATOR</b>	With Striker
<b>FUSE SIZE</b>	51 x 254 mm
<b>BREAKING CAPACITY</b>	20 kA
<b>INSTALLATION TECHNIQUE</b>	Air
<b>PERFORMANCE CAT ACCORDING TO IEC 60282-1</b>	Back-up
<b>RATED FREQUENCY - MAX</b>	50 Hz
<b>RATED FREQUENCY - MIN</b>	50 Hz
<b>RELEASE CHARACTERISTIC</b>	Other
<b>STANDARD</b>	British Standard
<b>VOLTAGE TYPE</b>	AC
<b>WITH STRIKER</b>	Yes
<b>CLASS</b>	Class back-up
<b>FUSE SHAPE</b>	Cylindrical, offset bolted tags
<b>PRE ARC (I2T)</b>	3.8 x 102
<b>RESISTANCE</b>	22.8 ohms
<b>INTERRUPT RATING</b>	20 kAIC
<b>CONSTRUCTION SIZE</b>	51 x 254 mm
<b>MOUNTING METHOD</b>	Clip-in
<b>VOLTAGE RATING</b>	7.2 kV
<b>TYPE</b>	Fuse
<b>APPLICATION</b>	<ul style="list-style-type: none"> <li>• protection of primary side transformers</li> <li>• used in fuse switch combination units, fuse bases and fuse switches</li> </ul>
<b>FUSE TYPE</b>	ADFH

