



## Eaton 7.2WFMSJ125

Motor fuse-link, medium voltage, 125 A, AC 7.2 kV, DIN 43625 3", 76 x 442 mm, back-up, DIN, with striker HS

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series medium voltage motor fuse
<b>CATALOG NUMBER</b>	7.2WFMSJ125
<b>UPC</b>	051712501255
<b>PRODUCT LENGTH/DEPTH</b>	442 mm
<b>PRODUCT HEIGHT</b>	76 mm
<b>PRODUCT WIDTH</b>	76 mm
<b>PRODUCT WEIGHT</b>	5200 g
<b>COMPLIANCES</b>	VDE 0670-4 DIN 43625
<b>CERTIFICATIONS</b>	IEC60282-1



Powering Business Worldwide

<b>USED WITH</b>	A3354730 Nickel-plated copper fuse clip
<b>AMPERAGE RATING</b>	25 A
<b>FUSE INDICATOR</b>	Non Indicating
<b>FUSE SIZE</b>	76 x 442 mm
<b>BREAKING CAPACITY</b>	63 A
<b>INSTALLATION TECHNIQUE</b>	Air
<b>PERFORMANCE CAT ACCORDING TO IEC 60282-1</b>	Back-up
<b>PRODUCT APPLICATION</b>	Motor protection
<b>RATED FREQUENCY - MAX</b>	50 Hz
<b>RATED FREQUENCY - MIN</b>	50 Hz
<b>RELEASE CHARACTERISTIC</b>	Other
<b>STANDARD</b>	DIN
<b>UTILIZATION CATEGORY</b>	Other
<b>VOLTAGE TYPE</b>	AC
<b>WITH STRIKER</b>	Yes
<b>CLASS</b>	Class back-up
<b>BARRELS</b>	1
<b>FUSE SHAPE</b>	Cylindrical
<b>WATT LOSSES</b>	70 W
<b>RESISTANCE</b>	3.19 ohms
<b>FUSE DIAMETER</b>	76 mm
<b>INTERRUPT RATING</b>	63 kAIC
<b>CONSTRUCTION SIZE</b>	76 x 442 mm
<b>PACKAGING TYPE</b>	Standard
<b>VOLTAGE RATING</b>	7.2 kV
<b>TYPE</b>	fuse
<b>APPLICATION</b>	Motor protection
<b>FUSE TYPE</b>	WFMSJ

