


Eaton 7.2WKMSJ200

Motor fuse-link, medium voltage, 200 A, AC 7.2 kV, DIN 43625 3", 76 x 442 mm, back-up, DIN, with striker HS

PRODUCT NAME	Eaton Bussmann series medium voltage motor fuse
CATALOG NUMBER	7.2WKMSJ200
UPC	051712837798
PRODUCT LENGTH/DEPTH	442 mm
PRODUCT HEIGHT	76 mm
PRODUCT WIDTH	76 mm
PRODUCT WEIGHT	5200 g
COMPLIANCES	VDE 0670-4 DIN 43625
CERTIFICATIONS	IEC60282-1

USED WITH	A3354730 Nickel-plated copper fuse clip
AMPERAGE RATING	200 A
FUSE INDICATOR	Non Indicating
FUSE SIZE	76 x 442 mm
BREAKING CAPACITY	63 A
INSTALLATION TECHNIQUE	Air
PERFORMANCE CAT ACCORDING TO IEC 60282-1	Back-up
PRODUCT APPLICATION	Motor protection
RATED FREQUENCY - MAX	50 Hz
RATED FREQUENCY - MIN	50 Hz
RELEASE CHARACTERISTIC	Other
STANDARD	DIN
UTILIZATION CATEGORY	Other
VOLTAGE TYPE	AC
WITH STRIKER	Yes
CLASS	Class back-up
BARRELS	1
FUSE SHAPE	Cylindrical
WATT LOSSES	99 W
RESISTANCE	1.79 ohms
FUSE DIAMETER	76 mm
INTERRUPT RATING	63 kAIC
CONSTRUCTION SIZE	76 x 442 mm
PACKAGING TYPE	Standard
VOLTAGE RATING	7.2 kV
TYPE	fuse
APPLICATION	Motor protection
FUSE TYPE	WKMSJ



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
: