



Eaton 7092319FUL-0355

Eaton, Alarms & signalling devices, Fulleon, X10 Maxi sounder beacon housing, 10-60V AC-DC, Dark grey housing (X10/CE/MAH/G1/10-60 VAC-DC)

□□□□

PRODUCT NAME	Eaton X10 Industrial sounder and sounder beacon
CATALOG NUMBER	7092319FUL-0355
PRODUCT LENGTH/DEPTH	158 mm
PRODUCT HEIGHT	208 mm
PRODUCT WIDTH	196 mm
PRODUCT WEIGHT	1.729 kg
COMPLIANCES	EN



Powering Business Worldwide



NOMINAL VOLTAGE - MAX	60 V
NOMINAL VOLTAGE - MIN	10 V
TYPE OF CURRENT	AC/DC
ELECTRICITY CONSUMPTION	0.585 A
POWER	14.1 W
LENS COLOR	Other
LAMP TYPE	LED
SOUND OUTPUT	120 dB
TYPE OF OPTICAL SIGNAL	Flash light
TYPE OF ACOUSTIC SIGNAL DEVICE	Siren
TYPE OF ACOUSTIC SIGNAL	Pulse tone/continuous tone
MOUNTING METHOD	Surface mounting
COLOR HOUSING	Grey
FREQUENCY SOUND SIGNAL - MAX	2900 Kilo Hertz
FREQUENCY SOUND SIGNAL - MIN	125 Kilo Hertz
ALARM CURRENT - MAX	620 mA
ALARM CURRENT - MIN	550 mA
CONSTRUCTION MATERIAL	PC
HUMIDITY (NON CONDENSING) - MAX	95 %
HUMIDITY (NON CONDENSING) - MIN	0 %
IMPACT STRENGTH	IK08
OPERATING TEMPERATURE - MAX	75 °C
OPERATING TEMPERATURE - MIN	-30 °C
SYSTEM TYPOLOGY	Conventional (Non-addressable)
VOICE TONES	No
DEGREE OF PROTECTION	IP66
SUITABLE FOR	Ceiling Mounting Wall Mounting
CABLE ENTRY	M20 hole
SYSTEM WIRING	0.28 - 2.5 mm
COMPATIBLE WITH APPLE HOMEKIT	NO



