

Eaton 7092329FUL-0365

Eaton, Alarms & signalling devices, Fulleon, X10 Midi sounder, 10-60V AC-DC, Light grey housing (X10 /CE/MD/G2/10-60 VAC-DC)

PRODUCT NAME	Eaton X10 Industrial sounder and sounder beacon
CATALOG NUMBER	7092329FUL-0365
PRODUCT LENGTH/DEPTH	133 mm
PRODUCT HEIGHT	144 mm
PRODUCT WIDTH	165 mm
PRODUCT WEIGHT	0.658 kg
CERTIFICATIONS	Not Applicable

NUMBER OF TONES	102
COLOR HOUSING	Grey
MATERIAL HOUSING	Plastic
SOUND OUTPUT	110 dB
NOMINAL VOLTAGE	24 V
TYPE OF CURRENT	AC/DC
ELECTRICITY CONSUMPTION	0.045 A
ADDRESSING MODE	Hard addressing
ALARM CURRENT	100 mA
CONSTRUCTION MATERIAL	PC
IMPACT STRENGTH	IK08
OPERATING TEMPERATURE - MAX	70 °C
OPERATING TEMPERATURE - MIN	-40 °C
SYSTEM TOPOLOGY	Conventional (Non-Addressable)
TONES	102
VOICE TONES	No
PRODUCT BRANDING	Eaton
HUMIDITY (NON CONDENSING) - MAX	95 %
HUMIDITY (NON CONDENSING) - MIN	0 %
DEGREE OF PROTECTION	IP66
CABLE ENTRY	M20 hole
SYSTEM WIRING	0.5 - 2.5 mm

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

: