

## Eaton 740ASMYEL-24V

Eaton Crouse-Hinds series Pauluhn 740/741 spot light, Incandescent lamp, Heat resistant glass lens, Copper-free aluminum, Surface mount, Medium optical distribution, Yellow colored lens, 24 Vdc, 200W

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series Pauluhn 740/741 spot light
<b>CATALOG NUMBER</b>	740ASMYEL-24V
<b>UPC</b>	662276386488
<b>PRODUCT LENGTH/DEPTH</b>	8.75 in
<b>PRODUCT HEIGHT</b>	11.69 in
<b>PRODUCT WIDTH</b>	8.19 in
<b>PRODUCT WEIGHT</b>	7.5 lb

## Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	4
INGRESS PROTECTION (IP) RATINGS	IP66

## Product specifications

MATERIAL	Copper-free aluminum
WATTAGE	200W
LAMP TYPE	Incandescent
OPTICAL DISTRIBUTION	Medium
MOUNTING METHOD	Surface
VOLTAGE RATING	24 Vdc
LENS MATERIAL	Heat resistant glass
SPECIAL FEATURES	Yellow colored lens

[IF LBL1481 - 740 Industrial Spot Lights](#)

[IF LBL1482 - Lens Replacement for 746M Industrial Spot Lights](#)

[Eaton Specification Sheet - 740ASMYEL-24V](#)

[Crouse-Hinds Pauluhn 700 Series Industrial Spot Lights catalog page](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

