



Eaton 800NHG4B-690

Fuse-link, LV, 800 A, AC 690 V, NH4, gL/gG, IEC, single indicator, live gripping lugs

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage NH Fuse
CATALOG NUMBER	800NHG4B-690
UPC	051712515276
PRODUCT LENGTH/DEPTH	200 mm
PRODUCT HEIGHT	115 mm
PRODUCT WIDTH	102 mm
PRODUCT WEIGHT	2668 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC 60269-1 IEC 60269-2 DIN 43620

AMPERAGE RATING	800 A
FITTED WITH:	Metal gripping lugs
FUSE SIZE	NH4
CURRENT TYPE	AC
BREAKING CAPACITY	120 kA
RATED SWITCHING CAPACITY	120 kA
RATED VOLTAGE AC	690 V
CLASS	Class gG/gL
FUSE TYPE	Square body with knife blade contact
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
INTERRUPT RATING	120 kAIC
FUSE INDICATOR	Top fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	61 W
CONNECTION	Blade end
CONSTRUCTION	NH4
CONSTRUCTION SIZE	NH4
FUSE SHAPE	Slotted blade contacts Square body
VOLTAGE TYPE	AC
SUITABLE FOR	SD4-S NH Fuse base EBH Size 00 to 4 Horizontal fuse switch-disconnectors
MATERIAL	Ceramic body
QUANTITY	3
VOLTAGE RATING	690 V
TYPE	Fuse
APPLICATION	• industrial • Utilities, Solar, Wind
RATED SWITCHING CAPACITY AC	120 kA

