


Eaton 80AFE

Eaton Bussmann series high speed British standard fuse, 150 Vac/dc, 80A, None, Fuse

PRODUCT NAME	Eaton Bussmann series high speed british standard fuse
CATALOG NUMBER	80AFE
UPC	051712675611
PRODUCT LENGTH/DEPTH	100 mm
PRODUCT HEIGHT	22 mm
PRODUCT WIDTH	187 mm
PRODUCT WEIGHT	53.1 g
COMPLIANCES	Contact factory RoHS Compliant

AMPERAGE RATING	80 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
RATED SWITCHING CAPACITY	200 kA
RATED VOLTAGE AC	690 V
RATED VOLTAGE DC	500 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	76 mm
MOUNTING DIMENSION	M8
CURRENT TYPE	AC/DC
CLASS	Class aR
WATT LOSSES	20 W
FUSE SHAPE	Offset slotted bolted tags
COLOR	None
CONSTRUCTION SIZE	Other
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	AFE
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

