

Eaton 80KR85

Eaton Bussmann series low voltage british standard fuse, 80A, AC 415 V, system C type II, 23 x 57 mm, gL/gG

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	80KR85
PRODUCT LENGTH/DEPTH	57 mm
PRODUCT HEIGHT	22.2 mm
PRODUCT WIDTH	22.2 mm
PRODUCT WEIGHT	54.85 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	BS IEC 60269

AMPERAGE RATING	80 A
CURRENT TYPE	AC
BREAKING CAPACITY	33 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
RATED VOLTAGE AC	415 V
CLASS	Class gG/gL
FUSE TYPE	KR85
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
FUSE INDICATOR	Other
WATT LOSSES	5.4 W
CONNECTION	Ferrule end x ferrule end
CONSTRUCTION	BS system C type II
CONSTRUCTION SIZE	23 x 57 mm
FUSE SHAPE	Cylindrical
VOLTAGE TYPE	AC
MATERIAL	Ceramic
MOUNTING METHOD	Holder
RELEASE CHARACTERISTIC	Other
VOLTAGE RATING	415 V
TYPE	fuse
APPLICATION	protection of incoming cables into residential and commercial properties

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-standard-fuse-declaration-of-conformity-uk250979en.pdf](#)

Follow us on social media to get the latest product and support information.

