



□□□□

Eaton 80NC

Eaton Bussmann series high speed traction fuse, 80A, None, Fuse, Class C gL/gG

□□□□

PRODUCT NAME	Eaton Bussmann series high speed traction fuse
CATALOG NUMBER	80NC
UPC	051712838061
PRODUCT LENGTH/DEPTH	198 mm
PRODUCT HEIGHT	40 mm
PRODUCT WIDTH	50 mm
PRODUCT WEIGHT	581 g
COMPLIANCES	Contact factory



Powering Business Worldwide



AMPERAGE RATING	80 A
BREAKING CAPACITY	100 kA
VOLTAGE TYPE	DC
UTILIZATION CATEGORY	gG (cable protection/equipment protection)
RELEASE CHARACTERISTIC	Other
FUSE INDICATOR	None
FREQUENCY RATING - MIN	45 Hz
FREQUENCY RATING - MAX	62 Hz
RATED SWITCHING CAPACITY	100 A
CLASS	Class C gL/gG
WATT LOSSES	17 W
FUSE SHAPE	Center bolted tags
MOUNTING DIMENSION	M10
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	171 mm
CURRENT TYPE	DC
RATED VOLTAGE DC	750 V
COLOR	None
INTERRUPT RATING	100 kAIC
CONSTRUCTION SIZE	Other
MATERIAL	Ceramic
PACKAGING TYPE	Standard
VOLTAGE RATING	750 V
TYPE	Fuse
APPLICATION	traction
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other



DECLARATIONS OF CONFORMITY

[eaton-high-speed-traction-fuse-declaration-of-conformity-uk250895en.pdf](#)

