

Eaton 80NHFF00BI-400

Eaton Bussmann series Fuse-link, LV, 80 A, AC 400 V, NH00, gFF, IEC, dual indicator, insulated gripping lugs

| | |
|-------------------------|--|
| | |
| PRODUCT NAME | Eaton Bussmann series low voltage NH Fuse |
| CATALOG NUMBER | 80NHFF00BI-400 |
| PRODUCT LENGTH/DEPTH | 79 mm |
| PRODUCT HEIGHT | 57 mm |
| PRODUCT WIDTH | 30 mm |
| PRODUCT WEIGHT | 166 g |
| COMPLIANCES | CE Marked RoHS Compliant |
| CERTIFICATIONS | IEC 60269-1 IEC 60269-2 DIN 43620 |

| | |
|--------------------------------------|--|
| | |
| AMPERAGE RATING | 80 A |
| FITTED WITH: | Insulated metal gripping lugs |
| FUSE SIZE | NH00 |
| CURRENT TYPE | AC |
| BREAKING CAPACITY | 120 kA |
| FREQUENCY RATING - MAX | 62 Hz |
| FREQUENCY RATING - MIN | 45 Hz |
| RATED SWITCHING CAPACITY | 80 kA |
| RATED VOLTAGE AC | 400 V |
| CLASS | Class gFF |
| FUSE TYPE | Square body with knife blade contact |
| UTILIZATION CATEGORY | gFF(full-range, extra fast operation) |
| COLOR | None |
| INTERRUPT RATING | 80 kAIC |
| FUSE INDICATOR | Combination fuse status indicator |
| INSULATED METAL GRIPPING LUGS (IMGL) | Yes |
| WATT LOSSES | 8 W |
| CONNECTION | Blade end |
| CONSTRUCTION | NH00 |
| CONSTRUCTION SIZE | NH00 |
| FUSE SHAPE | Square body Knife blade contacts |
| VOLTAGE TYPE | AC |
| SUITABLE FOR | SD00-D Single pole NH Fuse base Microswitch 170H0236 TD00-D Triple pole NH Fuse base |
| MATERIAL | Ceramic body |
| QUANTITY | 3 |
| VOLTAGE RATING | 400 V |
| TYPE | Fuse |
| APPLICATION | industrial |
| FUSE SYSTEM (ACCORDING TO IEC) | Fuse system A |



60269)

**RATED SWITCHING
CAPACITY AC**

80 kA

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

