



Eaton 811011FULL-0005

Eaton, Alarms & signalling devices, Fulleon, Solista LED beacon, Red lens, Red housing, No base

□□□□

PRODUCT NAME	Eaton Solista Fire alarm beacon
CATALOG NUMBER	811011FULL-0005
PRODUCT LENGTH/DEPTH	34 mm
PRODUCT HEIGHT	93 mm
PRODUCT WIDTH	93 mm
PRODUCT WEIGHT	0.11 kg
COMPLIANCES	EN 50130-4:2011
CERTIFICATIONS	Not Applicable



Powering Business Worldwide



NOMINAL VOLTAGE	24 V
VOLTAGE TYPE	DC
ELECTRICITY CONSUMPTION	0.005 A
POWER	0.12 W
LENS COLOR	Red
MATERIAL HOUSING	Plastic
COLOR HOUSING	Other
MOUNTING METHOD	Surface mounting
NUMBER OF MODES	4
STANDBY-TIME UP TO	0 hour
AMBIENT TEMPERATURE - MAX	55 °C
AMBIENT TEMPERATURE - MIN	-10 °C
LAMP TYPE	LED not exchangeable
LAMP HOLDER	Other
DEGREE OF PROTECTION (IP)	IP33
ADDRESSING MODE	Hard addressing
ALARM CURRENT - MAX	10 mA
ALARM CURRENT - MIN	5 mA
CONSTRUCTION MATERIAL	ABS/FR
HUMIDITY (NON CONDENSING) - MAX	95 %
HUMIDITY (NON CONDENSING) - MIN	0 %
OPERATING TEMPERATURE - MAX	55 °C
OPERATING TEMPERATURE - MIN	-10 °C
STANDBY CURRENT	0
SYSTEM TYPOLOGY	Conventional (Non-addressable)
PRODUCT BRANDING	Eaton
NOMINAL VOLTAGE - MIN	12 V
NOMINAL VOLTAGE - MAX	24 V
ELECTRICITY CONSUMPTION - MIN	0.005 A
ELECTRICITY CONSUMPTION - MAX	0.01 A
INTEGRATED FUNCTION	Flashlight



