



□□□□

Eaton 8D717W35PNL

Aluminium jam nut receptacle, Olive drab cadmium plating, without male contacts, polarization N; 8D717W35PNL

□□□□

PRODUCT NAME	Eaton Souriau D38999 SIII / 8D series milaero connectors
CATALOG NUMBER	8D717W35PNL
PRODUCT LENGTH/DEPTH	32.5 mm
PRODUCT HEIGHT	41 mm
PRODUCT WIDTH	41 mm
PRODUCT WEIGHT	32 g



Powering Business Worldwide

□□□□

FITTED WITH:	Shielding
CONNECTOR ORIENTATION	N
CONNECTOR TYPE	
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Pin (Male)
COUPLING TYPE	
DEGREE OF PROTECTION	IP67
LAYOUT	35
PLATING	Cadmium
SHELL CONTINUITY	
SHELL MATERIAL	
SHELL SIZE	17
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	175 °C
OPERATING TEMPERATURE - MIN	-65 °C
RECEPTACLE TYPE	Jam Nut Receptacle
NUMBER OF CONTACTS	55
NUMBER OF CAVITY #22D	55
SALT SPRAY	500 hour
WORKING VOLTAGE (VRMS)	1300 V

□□

□□□□:

□□□□:

□□□:

□□: