

Eaton 8STA00609SN499

Aluminium oval flange receptacle, Black Zinc Nickel plating, with female contacts and M2 clinch nuts; 8STA00609SN499

PRODUCT NAME	Eaton Souriau 8STA series lightweight miniature connector
CATALOG NUMBER	8STA00609SN499
PRODUCT LENGTH/DEPTH	23.1 mm
PRODUCT HEIGHT	22.4 mm
PRODUCT WIDTH	14.8 mm
PRODUCT WEIGHT	4.6 g

ENVIRONMENTAL CONDITIONS	REACH RoHS
BACKSHELL TYPE	Shrink Boot Adapter
CONNECTOR ACCESSORY OPTION	Integrated with connector
CONNECTOR ORIENTATION	A
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Unloaded
CONTACT GENDER	Socket (Female)
CONTACT PLATING	Gold
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP67
INSERT MATERIAL	Peek
LAYOUT	9
PLATING	Black Zinc Nickel
SHELL MATERIAL	Aluminium
SHELL SIZE	6
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	175 °C
OPERATING TEMPERATURE - MIN	-55 °C
RECEPTACLE TYPE	Square Flange Receptacle
NUMBER OF CONTACTS	9
NUMBER OF CAVITY #26	9
SALT SPRAY	48 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

