



□□□□

Eaton 8STA11243PA

Aluminium in line receptacle, Black Zinc Nickel plating, with male contacts;
8STA11243PA

□□□□

PRODUCT NAME	Eaton Souriau 8STA series lightweight miniature connector
CATALOG NUMBER	8STA11243PA
PRODUCT LENGTH/DEPTH	33.5 mm
PRODUCT HEIGHT	25.1 mm
PRODUCT WIDTH	25.1 mm
PRODUCT WEIGHT	16.2 g

□□□□

FITTED WITH:	Shielding
ENVIRONMENTAL CONDITIONS	REACH RoHS
BACKSHELL TYPE	Shrink Boot Adapter
CONNECTOR ACCESSORY OPTION	Integrated with connector
CONNECTOR ORIENTATION	A
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Unloaded
CONTACT GENDER	Pin (Male)
CONTACT PLATING	Gold
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP67
INSERT MATERIAL	Peek
LAYOUT	43
PLATING	Black Zinc Nickel
SHELL CONTINUITY	10.0
SHELL MATERIAL	Aluminium
SHELL SIZE	12
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	175 °C
OPERATING TEMPERATURE - MIN	-55 °C
RECEPTACLE TYPE	In-Line Receptacle
NUMBER OF CONTACTS	43
NUMBER OF CAVITY #26	43
SALT SPRAY	48 hour

□□

