

Eaton 8STA12206SA

Aluminium in line receptacle, Black Zinc Nickel plating, with female contacts; 8STA12206SA

PRODUCT NAME	Eaton Souriau 8STA series lightweight miniature connector
CATALOG NUMBER	8STA12206SA
PRODUCT LENGTH/DEPTH	33.5 mm
PRODUCT HEIGHT	41.2 mm
PRODUCT WIDTH	41.2 mm
PRODUCT WEIGHT	77.6 g

FITTED WITH:	Shielding
ENVIRONMENTAL CONDITIONS	RoHS REACH
BACKSHELL TYPE	Shrink Boot Adapter
CONNECTOR ACCESSORY OPTION	Integrated with connector
CONNECTOR ORIENTATION	A
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Unloaded
CONTACT GENDER	Socket (Female)
CONTACT PLATING	Gold
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP67
INSERT MATERIAL	Peek
LAYOUT	6
PLATING	Black Zinc Nickel
SHELL CONTINUITY	10.0
SHELL MATERIAL	Aluminium
SHELL SIZE	22
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	175 °C
OPERATING TEMPERATURE - MIN	-55 °C
RECEPTACLE TYPE	In-Line Receptacle
NUMBER OF CONTACTS	6
NUMBER OF CAVITY #8 POWER	6
SALT SPRAY	48 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
: