


Eaton 8STA20635SN528

Aluminium oval flange receptacle, Black Zinc Nickel plating, with female PCB contacts and M2.5 clinch nuts; 8STA20635SN528

PRODUCT NAME	Eaton Souriau 8STA series lightweight miniature connector
CATALOG NUMBER	8STA20635SN528
PRODUCT LENGTH/DEPTH	23.1 mm
PRODUCT HEIGHT	22.4 mm
PRODUCT WIDTH	14.8 mm
PRODUCT WEIGHT	5 g

ENVIRONMENTAL CONDITIONS	REACH RoHS
BACKSHELL TYPE	Shrink Boot Adapter
CONNECTOR ACCESSORY OPTION	Integrated with connector
CONNECTOR ORIENTATION	A
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Socket (Female)
CONTACT PLATING	Gold
CONTACT TYPE	PCB
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP67
INSERT MATERIAL	Peek
LAYOUT	35
PLATING	Black Zinc Nickel
SHELL MATERIAL	Aluminium
SHELL SIZE	6
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	175 °C
OPERATING TEMPERATURE - MIN	-55 °C
RECEPTACLE TYPE	Oval Flange Receptacle
NUMBER OF CONTACTS	5
NUMBER OF CAVITY #22D	5
SALT SPRAY	48 hour



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

