

Eaton 9PX1000IRT2UANZ

Eaton 9PX UPS, ANZ, RT2U, 1000VA, 1000W, 240VAC, Input: IEC C14, Output: IEC C13 x 8, built-in battery, Multilingual graphical LCD display

PRODUCT NAME	Eaton 9PX UPS
CATALOG NUMBER	9PX1000IRT2UANZ
PRODUCT LENGTH/DEPTH	440 mm
PRODUCT HEIGHT	86.5 mm
PRODUCT WIDTH	450 mm
PRODUCT WEIGHT	17.4 kg
COMPLIANCES	CB CE Marked RCM
CERTIFICATIONS	IEC 61000-4 EN 62040-3 IEC/EN 62040-2 IEC/EN 62040-1

TOPOLOGY	Online/Double-conversion
FORM FACTOR	Rack/tower
CONSTRUCTION TYPE	482.6 mm (19 inch) device
COLOR	Black/silver
VA RATING	1000 VA
WATTAGE	1000 W
INTERNAL BYPASS	Yes
HOT SWAP POWER	No
AUTO SHUTDOWN FUNCTION	Yes
INPUT NOMINAL VOLTAGE	240V
NOMINAL FREQUENCY	50/60 Hz
INPUT FREQUENCY RANGE	40-70 Hz
RECEPTACLE	IEC C13 x 8
OUTPUT WAVEFORM	Sine wave
VOLTAGE	240V
OUTPUT NOMINAL VOLTAGE	240V
VOLTAGE TYPE	AC
RUNTIME GRAPH	View runtime graph
BATTERY REPLACEMENT	Hot swappable
BATTERY TYPE	Sealed, lead-acid
EXTENDED BATTERY CAPABILITY	Yes
EXPANSION SLOTS	One slot for optional communication card
INCLUDES NETWORK CARD	No
SOFTWARE COMPATIBILITY	Eaton Intelligent Power Manager, Eaton Intelligent Power Protector
USER INTERFACE	Multilingual graphical LCD display
ALTITUDE	<1000m for nominal power, 10% power degrading every 1000m (up to 3000m)
NOISE LEVEL	<35 dB at 1 meter
RELATIVE HUMIDITY	0-96% non-condensing
TEMPERATURE RANGE	0° to 40°C (32° to 104°F)
INPUT VOLTAGE RANGE	176-276 Vac without



	derating (up to 100-276 Vac with derating)
OUTPUT FREQUENCY	50/60 Hz
OUTPUT POWER FACTOR	1.0
PHASE (INPUT)	Single-phase
PHASE (OUTPUT)	Single-phase

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

