



□□□□

Eaton 9PX1500IRTN-L

Eaton 9PX Lithium UPS Netpack, 1500 VA, 1500 W, Input: C14, Outputs: (8) C13, Rack/tower, 2U, Network card included

□□□□

PRODUCT NAME	Eaton 9PX UPS
CATALOG NUMBER	9PX1500IRTN-L
UPC	743172105837
PRODUCT LENGTH/DEPTH	450 mm
PRODUCT HEIGHT	86.5 mm
PRODUCT WIDTH	440 mm
PRODUCT WEIGHT	15.9 kg
COMPLIANCES	CE Marked



Powering Business Worldwide

SPECIAL FEATURES

- Lithium-ion batteries
- Double conversion topology
- Constantly monitors power conditions and regulates voltage and frequency
- First UPS in its class to provide Unity power factor (VA=W)
- Energy Star qualified, provides the highest efficiency level to reduce energy and cooling costs
- Internal bypass allows service continuity in case of UPS fault
- Next-generation graphical LCD display
- Network card and rackmounting kit delivered as standard
- Compatible with Virtual environments (VMware, Hyper-V, Citrix Xen, Redhat)
- Meter energy consumption (down to the managed outlet groups)

TOPOLOGY	Online/Double-conversion
RACK SIZE	2U
CONSTRUCTION TYPE	482.6 mm (19 inch) device
COLOR	Black/silver
VA RATING	1500 VA
WATTAGE	1500 W
RACK MOUNTING KIT	Yes

PACKAGE CONTENTS

- UPS
- Network Management Card
- (2) IEC-IEC output cables

- USB cable
- Serial cable
- (2) brackets for 19' mounting
- (2) Rack-mounting kit
- (2) Supports for tower mounting
- Cable locking system
- Safety instructions
- Quickstart guide

INTERNAL BYPASS	Yes
HOT SWAP POWER	No
AUTO SHUTDOWN FUNCTION	Yes
PRIMARY FREQUENCY - MAX	70 Hz
PRIMARY FREQUENCY - MIN	40 Hz
INPUT CONNECTION	C14
INPUT NOMINAL VOLTAGE	230V default (200/208/220/230/240V)
NOMINAL FREQUENCY	50/60 Hz
INPUT FREQUENCY RANGE	40-70 Hz
INPUT POWER FACTOR	>.99
RECEPTACLE	(8) C13
NUMBER OF OUTPUT CONNECTIONS FRENCH STANDARD (TYPE E)	0
NUMBER OF OUTPUTS C13	8
NUMBER OF OUTPUTS C19	0
NUMBER OF OUTPUTS HARDWIRED	0
NUM OF OUTPUTS PC (SCHUKO)	0
OUTPUT WAVEFORM	Sine wave
VOLTAGE	230V
OUTPUT NOMINAL VOLTAGE	230V default (200/208/220/230/240V)
FEED TYPE	1
VOLTAGE TYPE	AC
RUNTIME GRAPH	\$row.attributeValue.cdata
BATTERY MANAGEMENT	• Lithium-ion

	<p>batteries with battery management system</p> <ul style="list-style-type: none"> • Automatic recognition of external battery units
BATTERY REPLACEMENT	Hot-swappable internal batteries and extended battery modules (EBMs)
BATTERY TYPE	Lithium-ion
EXTENDED BATTERY CAPABILITY	Yes
RUNTIME AT HALF LOAD	21.5 min
COMMUNICATION	<ul style="list-style-type: none"> • USB port (HID compliant) • Serial port (RS232) • Mini terminal block for remote On/Off • Mini-terminal block for remote power off • Mini-terminal block for output relay • Dry contacts (3 outputs, 1 input, optocoupler, DB9)
EXPANSION SLOTS	One slot, network card included
ETHERNET INTERFACE	Yes
INCLUDES NETWORK CARD	Yes
SOFTWARE COMPATIBILITY	Eaton Intelligent Power Manager, Eaton Intelligent Power Protector
USER INTERFACE	Multilingual graphical LCD display
TYPE OF INTERFACE	Other
POTENTIAL FREE SWITCH CONTACT	Yes
ALTITUDE	3000 m
BTU RATING	Online: 386
NOISE LEVEL	<35 dB at 1 meter
RELATIVE HUMIDITY	0-96% non-condensing
TEMPERATURE RANGE	0° to 40°C (32° to 104°F)
PROTOCOL	SNMP
INTEGRATED FUNCTIONALITY	Network Management

