



□□□□

Eaton 9PX2200IRT2UANZ

Eaton 9PX UPS, ANZ, RT2U, 2200VA, 2200W, 240VAC, Input: IEC C14, Output: IEC C13 x 8 and IEC C19 x 2, built-in battery, Multilingual graphical LCD display

□□□□

PRODUCT NAME	Eaton 9PX UPS
CATALOG NUMBER	9PX2200IRT2UANZ
PRODUCT LENGTH/DEPTH	440 mm
PRODUCT HEIGHT	86.5 mm
PRODUCT WIDTH	605 mm
PRODUCT WEIGHT	25.02 kg
COMPLIANCES	RCM CE Marked CB
CERTIFICATIONS	IEC/EN 62040-1 IEC/EN 62040-2 IEC 61000-4 EN 62040-3



Powering Business Worldwide

TOPOLOGY	Online/Double-conversion
CONSTRUCTION TYPE	482.6 mm (21 inch) device
COLOR	Black/silver
VA RATING	2200 VA
WATTAGE	2200 W
INTERNAL BYPASS	Yes
HOT SWAP POWER	No
AUTO SHUTDOWN FUNCTION	Yes
INPUT NOMINAL VOLTAGE	240V
NOMINAL FREQUENCY	50/60 Hz
INPUT FREQUENCY RANGE	40-70 Hz
RECEPTACLE	IEC C13 x 8, IEC C19 x 2
OUTPUT WAVEFORM	Sine wave
VOLTAGE	240V
OUTPUT NOMINAL VOLTAGE	240V
VOLTAGE TYPE	AC
RUNTIME GRAPH	View runtime graph
BATTERY REPLACEMENT	Hot swappable
BATTERY TYPE	Sealed, lead-acid
EXTENDED BATTERY CAPABILITY	Yes
EXPANSION SLOTS	One slot for optional communication card
INCLUDES NETWORK CARD	No
SOFTWARE COMPATIBILITY	Eaton Intelligent Power Manager, Eaton Intelligent Power Protector
USER INTERFACE	Multilingual graphical LCD display
ALTITUDE	<1000m for nominal power, 10% power degrading every 1000m (up to 3000m)
NOISE LEVEL	<40 dB at 1 meter
RELATIVE HUMIDITY	0-96% non-condensing
TEMPERATURE RANGE	0° to 40°C (32° to 104°F)
INPUT VOLTAGE RANGE	176-276 Vac without derating (up to 100-276 Vac with derating)
OUTPUT FREQUENCY	50/60 Hz

