

Eaton 9PX3000GRT

Eaton 9PX UPS, 2U, 3000 VA, 3000 W, L6-20P input, 208V, Outputs: (8) C13, (2) C19

PRODUCT NAME	Eaton 9PX UPS
CATALOG NUMBER	9PX3000GRT
UPC	743172081308
PRODUCT LENGTH/DEPTH	23.8 in
PRODUCT HEIGHT	3.4 in
PRODUCT WIDTH	17.3 in
PRODUCT WEIGHT	60.4 lb
COMPLIANCES	IEC 62040-2 Cat C1 CISPR22 Class B FCC part 15 Class B CE Marked
CERTIFICATIONS	cULus Listed ENERGY STAR certified

TOPOLOGY	Online/Double-conversion
FORM FACTOR	Rack/tower
RACK SIZE	2U
COLOR	Black/silver
VA RATING	3000 VA
WATTAGE	3000 W
RACK MOUNTING KIT	Yes
PACKAGE CONTENTS	<ul style="list-style-type: none">• 9PX3000GLRT UPS• Input cable• 4-post rail kit• Safety manual• User manual• Tower pedestals• RS-232 serial cable• USB cable• Intelligent Power Software Suite CD
INTERNAL BYPASS	Yes
INPUT CONNECTION	L6-20P
INPUT CORD LENGTH	6 ft detachable
INPUT NOMINAL VOLTAGE	208V default (200/208/220/230/240V)
INPUT FREQUENCY RANGE	60 Hz: 50–70 Hz, 50 Hz: 40–60 Hz
INPUT POWER FACTOR	>0.99 typical
RECEPTACLE	(8) C13, (2) C19
NUMBER OF OUTPUTS C13	8
NUMBER OF OUTPUTS C19	2
OUTPUT WAVEFORM	True sine wave
VOLTAGE	208 V
OUTPUT NOMINAL VOLTAGE	208V default (200/208/220/230/240V)
RUNTIME GRAPH	\$row.attributeValue.cdata
BATTERY MANAGEMENT	ABM technology (3-stage charging extends battery service life by 50% and provides advance warning for battery replacement)
BATTERY REPLACEMENT	Hot-swappable internal batteries and extended battery modules (EBMs)
BATTERY TYPE	Sealed, lead-acid



EXTENDED BATTERY CAPABILITY	Add up to 4 extended battery modules (EBM). Part number 9PXEBM72RT
STANDARD FACTORY WARRANTY	<ul style="list-style-type: none"> • 3-YEAR FACTORY WARRANTY • - 3 years • - Parts, electronics and batteries coverage • - Standard ground shipping • - Technical support
EXTENDED SERVICE PLANS	<ul style="list-style-type: none"> • ADVANCED DEPOT EXCHANGE • - 5-year depot repair: 9SW5Y-3000UC • - Expedited parts coverage for 5 years • - Parts, electronics and UPS batteries coverage • - Next business day shipping • - Technical support • • 5-YEAR ON-SITE PLAN: WFLN75XX-6009UC • - On-site parts and labor coverage for years 5 • - Parts, electronics and UPS batteries coverage • - 24x7 on-site labor coverage, next-day response • - Next-day shipping • - Technical support
COMMUNICATION	RS-232 (RJ45), USB (HID)
EXPANSION SLOTS	<ul style="list-style-type: none"> • (1) Mini-Slot (MS) expansion port. The following optional connectivity cards may be ordered separately. • Gigabit Network Card part number:

-
- NETWORK-M3
- Modbus card part number: INDGW-M2
 - Relay card part number: RELAY-MS

SOFTWARE COMPATIBILITY	Intelligent Power Software Suite
USER INTERFACE	Graphical display, 5-button programmable menu
ALTITUDE	0-1500m (0° to 40°C), 1500-3000m (0° to 35°C)
BTU RATING	Online: 513, Battery: 741
NOISE LEVEL	<47 dB at 1 meter
RELATIVE HUMIDITY	0-96% non-condensing
TEMPERATURE RANGE	0° to 40°C (32° to 104°F)
EFFICIENCY AT MAX. LOAD	93%
MAX NUMBER OF BATTERY PACKS	4
OUTPUT FREQUENCY	50/60 Hz
OUTPUT POWER FACTOR	1
OUTPUT VOLTAGE RANGE	±1% steady-state
RUNTIME AT FULL LOAD	6 min

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

