



□□□□

## Eaton 9PX3000RT

Eaton 9PX UPS, 2U, 3000 VA, 2700 W, L5-30P input, Outputs: (6) 5-20R, (1) L5-30R, 120V

□□□□

<b>PRODUCT NAME</b>	Eaton 9PX UPS
<b>CATALOG NUMBER</b>	9PX3000RT
<b>UPC</b>	743172081285
<b>PRODUCT LENGTH/DEPTH</b>	23.8 in
<b>PRODUCT HEIGHT</b>	3.4 in
<b>PRODUCT WIDTH</b>	17.3 in
<b>PRODUCT WEIGHT</b>	63.1 lb
<b>COMPLIANCES</b>	IEC 62040-2 Cat C1 CISPR22 Class B FCC part 15 Class B VCCI Class B CE Marked
<b>CERTIFICATIONS</b>	cULus Listed NOM ENERGY STAR certified ICC-ES AC156 OSHPD Seismic certified



Powering Business Worldwide



<b>TOPOLOGY</b>	Online/Double-conversion
<b>RACK SIZE</b>	2U
<b>COLOR</b>	Black/silver
<b>VA RATING</b>	3000 VA
<b>WATTAGE</b>	2700 W
<b>RACK MOUNTING KIT</b>	Yes

**PACKAGE CONTENTS**

- 9PX3000RT UPS
- 4-post rail kit
- Safety manual
- User manual
- Tower pedestals
- RS-232 serial cable
- USB cable
- Intelligent Power Software Suite CD

<b>INTERNAL BYPASS</b>	Yes
<b>INPUT CONNECTION</b>	L5-30P
<b>INPUT CORD LENGTH</b>	8 ft
<b>INPUT NOMINAL VOLTAGE</b>	120V default (100/110/120/125V)
<b>INPUT FREQUENCY RANGE</b>	60 Hz: 50–70 Hz, 50 Hz: 40–60 Hz
<b>INPUT POWER FACTOR</b>	>0.99 typical
<b>RECEPTACLE</b>	(6) 5-20R, (1) L5-30R
<b>NUMBER OF OUTPUTS 5-20R</b>	6
<b>NUMBER OF OUTPUTS L5-30R</b>	1
<b>OUTPUT WAVEFORM</b>	True sine wave
<b>VOLTAGE</b>	120V
<b>OUTPUT NOMINAL VOLTAGE</b>	120V default (100/110/120/125V)
<b>RUNTIME GRAPH</b>	\$row.attributeValue.cdata
<b>BATTERY MANAGEMENT</b>	ABM technology (3-stage charging extends battery service life by 50% and provides advance warning for battery replacement)
<b>BATTERY REPLACEMENT</b>	Hot-swappable internal batteries and extended battery modules (EBMs)
<b>BATTERY TYPE</b>	Sealed, lead-acid
<b>EXTENDED BATTERY CAPABILITY</b>	Add up to 4 extended battery modules (EBM). Part number 9PXEBM72RT



---

**STANDARD FACTORY WARRANTY**

- 3-YEAR FACTORY WARRANTY
- - 3 years
- - Parts, electronics and batteries coverage
- - Standard ground shipping
- - Technical support

**EXTENDED SERVICE PLANS**

- ADVANCED DEPOT EXCHANGE
- - 5-year depot repair: 9SW5Y-3000UC
- - Expedited parts coverage for 5 years
- - Parts, electronics and UPS batteries coverage
- - Next business day shipping
- - Technical support
- 
- 5-YEAR ON-SITE PLAN: WFLN75XX-6009UC
- - On-site parts and labor coverage for years 5
- - Parts, electronics and UPS batteries coverage
- - 24x7 on-site labor coverage, next-day response
- - Next-day shipping
- - Technical support

**COMMUNICATION**

MiniSlot + 1 USB port + 1 serial RS232 port + 1 mini-terminal block for remote ON/OFF + 1 mini-terminal block for remote power off + 1 mini-terminal block for output relay  
Communication slot

**EXPANSION SLOTS**

- (1) Mini-Slot (MS) expansion port. The following optional connectivity cards may be ordered separately.
  - Gigabit Network
-

	<p>Card part number: NETWORK-M3</p> <ul style="list-style-type: none"> <li>• Modbus card part number: INDGW-M2</li> <li>• Relay card part number: RELAY-MS</li> </ul>
<b>SOFTWARE COMPATIBILITY</b>	Intelligent Power Software Suite
<b>USER INTERFACE</b>	Graphical display, 5-button programmable menu
<b>ALTITUDE</b>	0-1500m (0° to 40°C), 1500-3000m (0° to 35°C)
<b>BTU RATING</b>	Online: 844, Battery: 1462
<b>NOISE LEVEL</b>	<47 dB at 1 meter
<b>RELATIVE HUMIDITY</b>	0-96% non-condensing
<b>TEMPERATURE RANGE</b>	0° to 40°C (32° to 104°F)
<b>PRODUCT HIGHLIGHTS</b>	<p>Keeps equipment running during outages to allow time for file saves and safe shutdown</p> <p>Optional NETWORK-M3 Gigabit network card enables full remote access and control</p> <p>NEMA outlets split into separate switched banks for managed load shedding</p> <p>Interactive LCD interface keeps you updated on critical load information in real time</p> <p>Optional extended battery modules allow extended runtime to keep equipment powered</p>
<b>EFFICIENCY AT MAX. LOAD</b>	91
<b>MAX NUMBER OF BATTERY PACKS</b>	4
<b>OUTPUT FREQUENCY</b>	50/60 Hz
<b>OUTPUT POWER FACTOR</b>	0.9
<b>OUTPUT VOLTAGE RANGE</b>	±1% steady-state
<b>RUNTIME AT FULL LOAD</b>	5 min

