



□□□□

Eaton 9PX3000RTN-L

Eaton 9PX lithium ion UPS, 2U, 3000VA, 2700W, L5-30P input, Outputs: (6) 5-20R, (1) L5-30R, 120V, network card included

□□□□

PRODUCT NAME	Eaton 9PX UPS
CATALOG NUMBER	9PX3000RTN-L
UPC	786689526184
PRODUCT LENGTH/DEPTH	23.8 in
PRODUCT HEIGHT	3.4 in
PRODUCT WIDTH	17.3 in
PRODUCT WEIGHT	53.7 lb
COMPLIANCES	FCC part 15 Class B IEC 62040-2 Cat C1
CERTIFICATIONS	cULus Listed NOM ICC-ES AC156 OSHPD Seismic certified



Powering Business Worldwide

SPECIAL FEATURES	Gigabit Network Card (NETWORK-M3) included
TOPOLOGY	Online/Double-conversion
RACK SIZE	2U
COLOR	Black/silver
VA RATING	3000 VA
WATTAGE	2700 W
RACK MOUNTING KIT	Yes
PACKAGE CONTENTS	<ul style="list-style-type: none"> • 3000VA 2700W 120V 9PX Online Double-Conversion UPS with 7 Outlets • NETWORK-M3 Gigabit network card • USB cable • RS-232 cable • Rack-mounting hardware • Tower support stands • Safety guide • Quick Start Guide
INTERNAL BYPASS	Yes
INPUT CONNECTION	L5-30P
INPUT CORD LENGTH	8 ft
INPUT NOMINAL VOLTAGE	120V default (100/110/120/125V)
INPUT FREQUENCY RANGE	60 Hz: 50-70 Hz, 50 Hz: 40-60 Hz
INPUT POWER FACTOR	>0.99 typical
RECEPTACLE	(6) 5-20R, (1) L5-30R, 120V
NUMBER OF OUTPUTS 5-20R	6
NUMBER OF OUTPUTS L5-30R	1
OUTPUT WAVEFORM	True sine wave
VOLTAGE	120V
OUTPUT NOMINAL VOLTAGE	208V default (200/208/220/230/240V)
RUNTIME GRAPH	\$row.attributeValue.cdata
BATTERY MANAGEMENT	Integrated battery management system (BMS) for temperature regulation and life cycle monitoring
BATTERY REPLACEMENT	Hot-swappable internal

	batteries and extended battery modules (EBMs). Replacement battery part # EBP-1609-L (qty 1 per UPS).
BATTERY TYPE	Lithium-ion
EXTENDED BATTERY CAPABILITY	Add up to 4 extended battery modules (EBM). Part number 9PXEBM72RT-L
STANDARD FACTORY WARRANTY	<ul style="list-style-type: none"> • 5-YEAR FACTORY WARRANTY • - 5 years • - Parts, electronics and batteries coverage • - Standard ground shipping • - Technical support
BATTERY CHEMISTRY	Lithium Iron Phosphate (LiFePo4)
COMMUNICATION	RS-232 (RJ45) ports; USB port as standard (HID). 6-foot RS-232 and USB cables included
EXPANSION SLOTS	(1) Mini-Slot (MS) expansion port with Gigabit Network Card (NETWORK-M3) included
ETHERNET INTERFACE	Yes
INCLUDES NETWORK CARD	Yes
SOFTWARE COMPATIBILITY	Intelligent Power Software Suite
USER INTERFACE	Graphical display, 5-button programmable menu
ALTITUDE	0-1500m (0° to 40°C), 1500-3000m (0° to 35°C)
BTU RATING	Online: 844, Battery: 1462
NOISE LEVEL	<47 dB at 1 meter
RELATIVE HUMIDITY	0-96% non-condensing
TEMPERATURE RANGE	0° to 40°C (32° to 104°F)
PROTOCOL	SNMP
PRODUCT HIGHLIGHTS	Keeps equipment running during outages to allow time for file saves and safe shutdown Improved lithium-ion batteries have service life up to 10 years - set it and forget it!

