



Eaton 9PX3K3UN

Eaton 9PX UPS, 3U, 3000 VA, 3000 W, L6-30P input, Outputs: (2) L6-20R, (2) L6-30R, 208V

□□□□

PRODUCT NAME	Eaton 9PX UPS
CATALOG NUMBER	9PX3K3UN
UPC	743172082565
PRODUCT LENGTH/DEPTH	28.4 in
PRODUCT HEIGHT	5.1 in
PRODUCT WIDTH	17.3 in
PRODUCT WEIGHT	106 lb
COMPLIANCES	CISPR22 Class A / FCC part 15 Class A CE Marked
CERTIFICATIONS	cULus Listed NOM ENERGY STAR certified



Powering Business Worldwide

SPECIAL FEATURES	Gigabit Network Card (NETWORK-M3) included
TOPOLOGY	Online/Double-conversion
RACK SIZE	3U
COLOR	Black/silver
VA RATING	3000 VA
WATTAGE	3000 W
RACK MOUNTING KIT	Yes
PACKAGE CONTENTS	<ul style="list-style-type: none"> • 3000VA 3000W 208V 9PX Online Double-Conversion UPS with 4 Outlets • NETWORK-M3 Gigabit network card • USB cable • RS-232 cable • Tower support stands • Cable gland for hardwire connection • Rack-mounting hardware (9RK) • Quick start guide
INTERNAL BYPASS	Yes
INPUT CONNECTION	L6-30P
INPUT CORD LENGTH	6 ft
INPUT NOMINAL VOLTAGE	208V default (200/208/220/230/240V)
INPUT FREQUENCY RANGE	60 Hz: 50-70 Hz, 50 Hz: 40-60 Hz
INPUT POWER FACTOR	>0.99 typical
RECEPTACLE	(2) L6-20R, (2) L6-30R
NUMBER OF OUTPUTS L6-20R	2
NUMBER OF OUTPUTS L6-30R	1
OUTPUT WAVEFORM	True sine wave
VOLTAGE	208 V
OUTPUT NOMINAL VOLTAGE	208V default (200/208/220/230/240/250V)
RUNTIME GRAPH	\$row.attributeValue.cdata
BATTERY MANAGEMENT	ABM technology (3-stage charging extends battery service life by 50% and provides advance warning for battery replacement)
BATTERY	Hot-swappable internal

REPLACEMENT	batteries and extended battery modules (EBMs)
BATTERY TYPE	Sealed, lead-acid
EXTENDED BATTERY CAPABILITY	Add up to 4 extended battery modules (EBM). Part numbers CBLADAPT180RT + 9PXEBM180RTG2
STANDARD FACTORY WARRANTY	<ul style="list-style-type: none"> • 3-YEAR FACTORY WARRANTY • - 3 years • - Parts, electronics and batteries coverage • - Standard ground shipping • - Technical support
EXTENDED SERVICE PLANS	<ul style="list-style-type: none"> • ADVANCED DEPOT EXCHANGE • - 5-year depot repair: 9SW5Y-3000UC • - Expedited parts coverage for 5 years • - Parts, electronics and UPS batteries coverage • - Next business day shipping • - Technical support • • 5-YEAR ON-SITE PLAN: WFLN75XX-6009UC • - On-site parts and labor coverage for years 5 • - Parts, electronics and UPS batteries coverage • - 24x7 on-site labor coverage, next-day response • - Next-day shipping • - Technical support
COMMUNICATION	Web/SNMP in MiniSlot expansion port + 1 USB port + 1 serial RS232 port + 1 mini-terminal block for remote ON/OFF + 1 mini-terminal block for remote power off + 1 mini-terminal block for output relay Communication slot
EXPANSION SLOTS	(1) Mini-Slot (MS) expansion port with Gigabit Network

