


Eaton 9PX3K3UNP2G2

Eaton 9PXG2 3000VA 3000W 200-240V input, 120/240V output Online Double-Conversion UPS - Hardwired Input / Output, Cybersecure Network Card, Maintenance Bypass, 6U Rack/Tower

PRODUCT NAME	Eaton 9PX UPS
CATALOG NUMBER	9PX3K3UNP2G2
UPC	037332294258
PRODUCT LENGTH/DEPTH	27 in
PRODUCT HEIGHT	10.2 in
PRODUCT WIDTH	17.3 in
PRODUCT WEIGHT	203 lb
COMPLIANCES	CISPR22 Class A / FCC part 15 Class A
CERTIFICATIONS	cULus Listed NOM ENERGY STAR certified

SPECIAL FEATURES	Gigabit Network Card (NETWORK-M3) included
TOPOLOGY	Online/Double-conversion
RACK SIZE	6U
COLOR	Black/silver
VA RATING	3000 VA
WATTAGE	3000 W
RACK MOUNTING KIT	Yes
PACKAGE CONTENTS	• 3000VA 3000W 120/208V 9PX G2 Online Double-Conversion UPS • 9PXPPDM2G2 PowerPass Distribution Module with Maintenance Bypass • NETWORK-M3 Gigabit network card • USB cable • RS-232 cable • Cable gland for hardwire connection • Rack-mounting hardware • Tower support stands • Quick Start Guide
SURGE PROTECTION	Yes
INTERNAL BYPASS	Yes
INPUT CONNECTION	Hardwired
INPUT NOMINAL VOLTAGE	208V default (200/208/220/230/240V)
INPUT FREQUENCY RANGE	60 Hz: 50–70 Hz, 50 Hz: 40–60 Hz
INPUT POWER FACTOR	>0.99 typical
RECEPTACLE	Hardwired
OUTPUT WAVEFORM	True sine wave
VOLTAGE	120/240V
RUNTIME GRAPH	\$row.attributeValue.cdata
BATTERY MANAGEMENT	ABM+ technology uses battery replacement analytics to predict when you should replace UPS batteries based on real-life usage and conditions.
BATTERY REPLACEMENT	Hot-swappable internal batteries and extended battery modules (EBMs). Replacement battery part # EBP-1805 (qty 1 per UPS)
BATTERY TYPE	Sealed, lead-acid
EXTENDED BATTERY CAPABILITY	Add up to 12 EBMs, part # 9PXEBM180RTG2
STANDARD FACTORY WARRANTY	• 3-YEAR FACTORY WARRANTY



- - 3 years
- - Parts, electronics and batteries coverage
- - Standard ground shipping
- - Technical support

EXTENDED SERVICE PLANS

- ADVANCED DEPOT EXCHANGE
- - 5-year depot repair: 9SW5Y-3000UC
- - Expedited parts coverage for 5 years
- - Parts, electronics and UPS batteries coverage
- - Next business day shipping
- - Technical support
-
- 5-YEAR ON-SITE PLAN: WFLN75XX-6009UC
- - On-site parts and labor coverage for years 5
- - Parts, electronics and UPS batteries coverage
- - 24x7 on-site labor coverage, next-day response
- - Next-day shipping
- - Technical support

RUNTIME AT HALF LOAD

18.5 min

EXPANSION SLOTS

(1) Mini-Slot (MS) expansion port with Gigabit Network Card (NETWORK-M3) included

ETHERNET INTERFACE

Yes

INCLUDES NETWORK CARD

Yes

SOFTWARE COMPATIBILITY

Brightlayer Data Centers suite

USER INTERFACE

Graphical display, 5-button programmable menu, LED indicator

ALTITUDE

3000 m

BTU RATING

Online: 415 BTU/hr, Battery: 471 BTU/hr, High Efficiency: 177 BTU/hr

NOISE LEVEL

<43 dB at 1 meter

RELATIVE HUMIDITY

0-95% non-condensing

TEMPERATURE RANGE

0° to 40°C (32° to 104°F)

PROTOCOL

SNMP

PRODUCT HIGHLIGHTS

Keeps equipment running during outages to allow time for file saves and safe shutdown
Best-in-class efficiency results

	in reduced energy costs and greenhouse gas emissions Included NETWORK-M3 Gigabit network card enables full remote access and control Exclusive ABM+ technology and analytics help you pinpoint when to replace batteries Optional extended battery modules allow extra runtime to keep equipment powered
EFFICIENCY AT MAX. LOAD	96%
MAX NUMBER OF BATTERY PACKS	12
OUTPUT FREQUENCY	50/60 Hz
OUTPUT POWER FACTOR	1.0
OUTPUT VOLTAGE RANGE	±1% steady-state
RUNTIME AT FULL LOAD	7.5 min. (3000W)
OPTIONAL MOUNTING ACCESSORY NOTES	"2 post rackmount (RK2PC) - Model 9PX3K3UNP2G2 requires 2 RK2PC for 2 post mounting, 1 per UPS and 1 per PPDM

:
:
:
:

