



Eaton 9PX8KHW

Eaton 9PX UPS, Network card included, 6U, 8 kVA, 7.2 kW, Hardwired input, Outputs: Hardwired, 208V

□□□□

PRODUCT NAME	Eaton 9PX UPS
CATALOG NUMBER	9PX8KHW
UPC	743172108739
PRODUCT LENGTH/DEPTH	27.6 in
PRODUCT HEIGHT	10.2 in
PRODUCT WIDTH	17.3 in
PRODUCT WEIGHT	190 lb
COMPLIANCES	CE Marked FCC Part 15 CISPR22 Class A / FCC part 15 Class A
CERTIFICATIONS	cULus Listed IEC 62040-2:2006 Cat C2 NOM ENERGY STAR certified



Powering Business Worldwide

SPECIAL FEATURES	Gigabit Network Card (NETWORK-M3) included
TOPOLOGY	Online/Double-conversion
RACK SIZE	6U
COLOR	Black/silver
VA RATING	8 kVA
WATTAGE	7.2 kW
RACK MOUNTING KIT	Yes
PACKAGE CONTENTS	<ul style="list-style-type: none"> • 9PX8KPM 8 kVA 3U UPS power module • 9PXEBM240RT 3U extended battery module • Gigabit Network Card (Network-M3) • 4-post rail kit • User manual • Quick start guide • Tower pedestals • ! • RS-232 serial cable • USB cable • Cable gland for hardwire connection
INTERNAL BYPASS	Yes
INPUT CONNECTION	Hardwired
INPUT NOMINAL VOLTAGE	208V default (200/208/220/230/240/250V)
INPUT FREQUENCY RANGE	60 Hz: 50–70 Hz, 50 Hz: 40–60 Hz
INPUT POWER FACTOR	>0.99 typical
RECEPTACLE	Hardwired
NUMBER OF OUTPUTS HARDWIRED	1
OUTPUT WAVEFORM	True sine wave
VOLTAGE	208 V
OUTPUT NOMINAL VOLTAGE	208V default (200/208/220/230/240/250V)
RUNTIME GRAPH	\$row.attributeValue.cdata
BATTERY MANAGEMENT	ABM technology (3-stage charging extends battery service life by 50% and provides advance warning for battery replacement)
BATTERY REPLACEMENT	Hot-swappable internal batteries and extended battery modules (EBMs)
BATTERY TYPE	Sealed, lead-acid

EXTENDED BATTERY CAPABILITY

Add up to 5 extended battery modules (EBM). Part number 9PXEBM240RT. Add up to 12 EBMs with 240V supercharger module SC240RT.

STANDARD FACTORY WARRANTY

- 3-YEAR FACTORY WARRANTY
 - - 3 years
 - - Parts, electronics and batteries coverage
 - - Standard ground shipping
 - - Technical support
-

EXTENDED SERVICE PLANS

- ADVANCED DEPOT EXCHANGE
 - - 5-year depot repair: 9SW5Y-11000UC
 - - Expedited parts coverage for 5 years
 - - Parts, electronics and UPS batteries coverage
 - - Next business day shipping
 - - Technical support
 -
 - 5-YEAR ON-SITE PLAN: WFLN75XX-11000UC
 - - On-site parts and labor coverage for years 5
 - - Parts, electronics and UPS batteries coverage
 - - 24x7 on-site labor coverage, next-day response
 - - Next-day shipping
 - - Technical support
-

COMMUNICATION

Web/SNMP in MiniSlot expansion port + 1 USB port + 1 serial RS232 port + 1 mini-terminal block for remote ON/OFF + 1 mini-terminal block for remote power off + 1 mini-terminal block for output relay
Communication slot

EXPANSION SLOTS

(1) Mini-Slot (MS) expansion port with Gigabit Network Card (NETWORK-M3) included
