



Eaton 9PXM12AAAAA

Eaton 9PXM UPS frame, 4-20 kVA (N+1),
Hardwired input, Hardwired output,
Rack/Tower, 21U, Online/Double-
conversion, Free standing model,
Black/silver, 110V/220V, 120V/208V,
120V/240V, 127V/220V

□□□□

PRODUCT NAME	Eaton 9PXM UPS
CATALOG NUMBER	9PXM12AAAAA
UPC	743172091390
PRODUCT LENGTH/DEPTH	34.5 in
PRODUCT HEIGHT	36.5 in
PRODUCT WIDTH	17.5 in
PRODUCT WEIGHT	170 lb
COMPLIANCES	TAA Compliant FCC Compliant
CERTIFICATIONS	IEC Rated cULus Listed

TOPOLOGY	Online/Double-conversion
RACK SIZE	21U
CONSTRUCTION TYPE	Free standing model
COLOR	Black/silver

PACKAGE CONTENTS	• 9PXM12AAAAA 9PXM 208/240V Online Double- Conversion UPS Cabinet • Mounting hardware • Owner's manual
-------------------------	--

INTERNAL BYPASS	Yes
------------------------	-----

HOT SWAP POWER	Yes
-----------------------	-----

AUTO SHUTDOWN FUNCTION	Yes
-----------------------------------	-----

INPUT CONNECTION	Hardwired
-------------------------	-----------

INPUT FREQUENCY RANGE	60 Hz: 50–70 Hz
----------------------------------	-----------------

INPUT POWER FACTOR	>0.99 typical
---------------------------	---------------

RECEPTACLE	Hardwired
-------------------	-----------

NUMBER OF OUTPUTS HARDWIRED	1
--	---

OUTPUT WAVEFORM	True sine wave
------------------------	----------------

VOLTAGE	120/208V
----------------	----------

OUTPUT NOMINAL VOLTAGE	110V/220V, 120V/208V, 120V/240V, 127V/220V
-----------------------------------	---

FEED TYPE	1
------------------	---

RUNTIME GRAPH	\$row.attributeValue.cdata
----------------------	----------------------------

BATTERY MANAGEMENT	ABM technology (3-stage charging extends battery service life by 50% and provides advance warning for battery replacement)
---------------------------	--

BATTERY REPLACEMENT	Hot-swappable internal batteries and extended battery modules (EBMs)
----------------------------	--

BATTERY TYPE	Sealed, lead-acid
---------------------	-------------------

EXTENDED BATTERY CAPABILITY	Yes
--	-----

STANDARD FACTORY WARRANTY	• 2-YEAR FACTORY WARRANTY • - 2 years • Parts, labor, electronics and batteries coverage*
--------------------------------------	---

- - Startup included
- - Parts, electronics and batteries coverage
- - Standard ground shipping
- - Technical support
- *if startup is performed by Eaton, if self-performed startup then just 90 days labor

EXTENDED SERVICE PLANS

- ADVANCED DEPOT EXCHANGE
- - 5-year depot repair: 9SW5Y-11000UC
- - Expedited parts coverage for 5 years
- - Parts, electronics and UPS batteries coverage
- - Next business day shipping
- - Technical support
-
- 5-YEAR ON-SITE PLAN: WFLN75XX-11000UC
- - On-site parts and labor coverage for years 5
- - Parts, electronics and UPS batteries coverage
- - 24x7 on-site labor coverage, next-day response
- - Next-day shipping
- - Technical support

EXPANSION SLOTS

- (2) Mini-Slot (MS) expansion ports. The following optional connectivity cards may be ordered separately.
- Gigabit Network Card part number: NETWORK-M2
- Modbus card part number: INDGW-M2

- Relay card part number: RELAY-MS

SOFTWARE COMPATIBILITY	Intelligent Power Software Suite
USER INTERFACE	5-Button Graphical User Interface
RELATIVE HUMIDITY	5-95% non-condensing
TEMPERATURE RANGE	0° to 40°C (32° to 104°F)
INPUT NOMINAL VOLTAGE	110 VAC 120 VAC 127 VAC 208 VAC 220 VAC 240 VAC
NOMINAL OUTPUT VOLTAGE	110V 120V 127V 208V 220V 240V
MAX NUMBER OF BATTERY PACKS	12
OUTPUT FREQUENCY	60 Hz
OUTPUT POWER FACTOR	0.9
OUTPUT CAPACITY (WATTS)	18000
INPUT NOMINAL VOLTAGE	110V/220V, 120V/208V, 120V/240V, 127V/220V

□□□□:
□□□□:
□□□:
□□: