



Eaton 9PXM12S8K

Eaton 9PXM UPS, 8 kVA scalable to 20 kVA (N+1), Hardwired input, Hardwired output, 208-240V, Rack/Tower, 14U

□□□□

PRODUCT NAME	Eaton 9PXM UPS
CATALOG NUMBER	9PXM12S8K
UPC	743172091482
PRODUCT LENGTH/DEPTH	34.5 in
PRODUCT HEIGHT	36.5 in
PRODUCT WIDTH	17.5 in
PRODUCT WEIGHT	378 lb
COMPLIANCES	TAA Compliant FCC Compliant
CERTIFICATIONS	IEC Rated cULus Listed

TOPOLOGY	Online/Double-conversion
RACK SIZE	21U
CONSTRUCTION TYPE	Free standing model
COLOR	Black/silver
VA RATING	8 kVA
WATTAGE	7.2 kW

PACKAGE CONTENTS

- 9PXM12S8K 9PXM 8000VA 7200W 208/240V Online Double-Conversion UPS Cabinet
- (2) 9PXMSPPM 9PXM split-phase power modules
- (4) 9PXMBAAT 9PXM internal battery modules
- NETWORK-M2 Gigabit network card
- Owner's manual

INTERNAL BYPASS	Yes
HOT SWAP POWER	Yes
AUTO SHUTDOWN FUNCTION	Yes
INPUT CONNECTION	Hardwired
INPUT FREQUENCY RANGE	60 Hz: 50–70 Hz
INPUT POWER FACTOR	>0.99 typical
RECEPTACLE	Hardwired
NUMBER OF OUTPUTS L6-20R	2
NUMBER OF OUTPUTS L6-30R	2
NUMBER OF OUTPUTS HARDWIRED	1
OUTPUT WAVEFORM	True sine wave
VOLTAGE	120/208V
OUTPUT NOMINAL VOLTAGE	110V/220V, 120V/208V, 120V/240V, 127V/220V
FEED TYPE	1
RUNTIME GRAPH	\$row.attributeValue.cdata
BATTERY MANAGEMENT	ABM technology (3-stage charging extends battery service life by 50% and provides advance warning for battery replacement)

BATTERY REPLACEMENT	Hot-swappable internal batteries and extended battery modules (EBMs)
BATTERY TYPE	Sealed, lead-acid
EXTENDED BATTERY CAPABILITY	Yes

STANDARD FACTORY WARRANTY

- 2-YEAR FACTORY WARRANTY
- - 2 years
- Parts, labor, electronics and batteries coverage*
- - Startup included
- - Parts, electronics and batteries coverage
- - Standard ground shipping
- - Technical support
- *if startup is performed by Eaton, if self-performed startup then just 90 days labor

EXTENDED SERVICE PLANS

- ADVANCED DEPOT EXCHANGE
- - 5-year depot repair: 9SW5Y-18000UC
- - Expedited parts coverage for 5 years
- - Parts, electronics and UPS batteries coverage
- - Next business day shipping
- - Technical support
-
- 5-YEAR ON-SITE PLAN: WFLN75XX-18000UC
- - On-site parts and labor coverage for years 5
- - Parts, electronics and UPS batteries coverage
- - 24x7 on-site labor coverage, next-day response
- - Next-day shipping
- - Technical support

EXPANSION SLOTS

- (2) Mini-Slot (MS) expansion ports.
The following optional connectivity cards may be ordered separately.
- Gigabit Network Card part number: NETWORK-M2
- Modbus card part number: INDGW-M2
- Relay card part number: RELAY-MS

SOFTWARE COMPATIBILITY	Intelligent Power Software Suite
USER INTERFACE	5-Button Graphical User Interface
RELATIVE HUMIDITY	5-95% non-condensing
TEMPERATURE RANGE	0° to 40°C (32° to 104°F)
INPUT NOMINAL VOLTAGE	110 VAC 120 VAC 127 VAC 208 VAC 220 VAC 240 VAC
NOMINAL OUTPUT VOLTAGE	110V 120V 127V 208V 220V 240V
MAX NUMBER OF BATTERY PACKS	12
OUTPUT FREQUENCY	60 Hz
OUTPUT POWER FACTOR	0.9
FEATURES	Flex Center
OUTPUT CAPACITY (WATTS)	7200
INPUT NOMINAL VOLTAGE	110V/220V, 120V/208V, 120V/240V, 127V/220V

