



Eaton 9PXM12SEBM

Eaton 9PXM 12-slot external battery enclosure

□□□□

PRODUCT NAME	Eaton 9PXM EBM
CATALOG NUMBER	9PXM12SEBM
UPC	743172091413
PRODUCT LENGTH/DEPTH	34.5 in
PRODUCT HEIGHT	36.5 in
PRODUCT WIDTH	17.5 in
PRODUCT WEIGHT	165 lb
COMPLIANCES	TAA Compliant FCC Compliant
CERTIFICATIONS	IEC Rated cULus Listed

TOPOLOGY	Online/Double-conversion
RACK SIZE	21U
CONSTRUCTION TYPE	Free standing model
COLOR	Black/silver

PACKAGE CONTENTS	• 9PXM12SEBM 12-Slot Standard External Battery Cabinet • Battery cables • Owner's manual
-------------------------	--

INPUT CONNECTION	Hardwired
INPUT NOMINAL VOLTAGE	110V/220V, 120V/208V, 120V/240V, 127V/220V
INPUT FREQUENCY RANGE	60 Hz: 50–70 Hz, 50 Hz: 40–60 Hz
INPUT POWER FACTOR	>0.99 typical

BATTERY MANAGEMENT	ABM technology (3-stage charging extends battery service life by 50% and provides advance warning for battery replacement)
---------------------------	--

BATTERY REPLACEMENT	Hot-swappable internal batteries and extended battery modules (EBMs)
----------------------------	--

BATTERY TYPE	Sealed, lead-acid
---------------------	-------------------

EXTENDED BATTERY CAPABILITY	Yes
------------------------------------	-----

EXTENDED SERVICE PLANS	• ADVANCED DEPOT EXCHANGE • - 5-year depot repair: 9SW5Y-18000BC • - Expedited parts coverage for 5 years • - Parts, electronics and UPS batteries coverage • - Next business day shipping • - Technical support • • 5-YEAR ON-SITE PLAN: WEBN75XX-18000BC • - On-site parts and labor coverage for years 5 • - Parts, electronics
-------------------------------	---

	and UPS batteries coverage - 24x7 on-site labor coverage, next-day response - Next-day shipping - Technical support
RELATIVE HUMIDITY	5-95% non-condensing
TEMPERATURE RANGE	0° to 40°C (32° to 104°F)
ACCESSORY CLASS	UPS Accessories
ACCESSORY TYPE	Battery Frame
MAX NUMBER OF BATTERY PACKS	24

□□□□:
□□□□:
□□□:
□□: