



Eaton 9PXM8S12K

Eaton 9PXM UPS, 12 kVA scalable to 16 kVA,
Hardwired input, Hardwired output, 208-
240V, Rack/Tower, 14U

□□□□

PRODUCT NAME	Eaton 9PXM UPS
CATALOG NUMBER	9PXM8S12K
UPC	743172091543
PRODUCT LENGTH/DEPTH	34.5 in
PRODUCT HEIGHT	25 in
PRODUCT WIDTH	17.5 in
PRODUCT WEIGHT	437 lb
COMPLIANCES	TAA Compliant FCC Compliant
CERTIFICATIONS	IEC Rated cULus Listed

TOPOLOGY	Online/Double-conversion
RACK SIZE	14U
CONSTRUCTION TYPE	Free standing model
COLOR	Black/silver
VA RATING	12 kVA
WATTAGE	10.8 kW

PACKAGE CONTENTS

- 9PXM8S12K 9PXM 12000VA 10800W 208/240V Online Double-Conversion UPS
- (3) 9PXMSPPM 9PXM split-phase power modules
- (6) 9PXMBAT 9PXM internal battery modules
- NETWORK-M2 Gigabit network card
- Owner's manual

INTERNAL BYPASS	Yes
HOT SWAP POWER	Yes
AUTO SHUTDOWN FUNCTION	Yes
INPUT CONNECTION	Hardwired
INPUT NOMINAL VOLTAGE	110V/220V, 120V/208V, 120V/240V, 127V/220V
INPUT FREQUENCY RANGE	60 Hz: 50–70 Hz
INPUT POWER FACTOR	>0.99 typical
RECEPTACLE	Hardwired
NUMBER OF OUTPUTS HARDWIRED	1
OUTPUT WAVEFORM	True sine wave
VOLTAGE	120/208V
OUTPUT NOMINAL VOLTAGE	110V/220V, 120V/208V, 120V/240V, 127V/220V
FEED TYPE	1
RUNTIME GRAPH	\$row.attributeValue.cdata
BATTERY MANAGEMENT	ABM technology (3-stage charging extends battery service life by 50% and provides advance warning for battery replacement)
BATTERY REPLACEMENT	Hot-swappable internal batteries and extended

	battery modules (EBMs)
BATTERY TYPE	Sealed, lead-acid
EXTENDED BATTERY CAPABILITY	Yes
STANDARD FACTORY WARRANTY	• 2-YEAR FACTORY WARRANTY • - 2 years • Parts, labor, electronics and batteries coverage* • - Startup included • - Parts, electronics and batteries coverage • - Standard ground shipping • - Technical support • *if startup is performed by Eaton, if self-performed startup then just 90 days labor
EXTENDED SERVICE PLANS	• ADVANCED DEPOT EXCHANGE • - 5-year depot repair: 9SW5Y-11000UC • - Expedited parts coverage for 5 years • - Parts, electronics and UPS batteries coverage • - Next business day shipping • - Technical support • • 5-YEAR ON-SITE PLAN: WFLN75XX-11000UC • - On-site parts and labor coverage for years 5 • - Parts, electronics and UPS batteries coverage • - 24x7 on-site labor coverage, next-day response • - Next-day shipping • - Technical support
EXPANSION SLOTS	• (2) Mini-Slot (MS)

	expansion ports. The following optional connectivity cards may be ordered separately. • Gigabit Network Card part number: NETWORK-M2 • Modbus card part number: INDGW- M2 • Relay card part number: RELAY-MS
--	---

SOFTWARE COMPATIBILITY	Intelligent Power Software Suite
USER INTERFACE	5-Button Graphical User Interface
RELATIVE HUMIDITY	5-95% non-condensing
TEMPERATURE RANGE	0° to 40°C (32° to 104°F)
MAX NUMBER OF BATTERY PACKS	8
OUTPUT FREQUENCY	60 Hz
OUTPUT POWER FACTOR	0.9
FEATURES	Flex Center

□□□□:
□□□□:
□□□:
□□: