



Eaton 9SX1500G

Eaton 9SX online, extended runtime UPS,
1500 VA, 1350 W, 208V, C14 input, Outputs:
(8) C13, 9.9"Hx6.3"Wx17.1"D, 41.9 lb.,
network card optional

□□□□

PRODUCT NAME	Eaton 9SX UPS
CATALOG NUMBER	9SX1500G
UPC	743172091291
PRODUCT LENGTH/DEPTH	17.1 in
PRODUCT HEIGHT	9.9 in
PRODUCT WIDTH	6.3 in
PRODUCT WEIGHT	37.3 lb
COMPLIANCES	FCC Compliant CE Marked
CERTIFICATIONS	cULus Listed ICC-ES AC156 OSHPD Seismic certified



Powering Business Worldwide

□□□□	
TOPOLOGY	Online/Double-conversion
RACK SIZE	0U
CONSTRUCTION TYPE	Free standing model
COLOR	Black
VA RATING	1500 VA
WATTAGE	1350 W
PACKAGE CONTENTS	• 9SX1500G Eaton 9SX Double-Conversion UPS • (2) C13-to-C14 adapters, 6 ft. (1.8 m) • USB cable • RS-232 cable • Quick start guide
INTERNAL BYPASS	Yes
INPUT CONNECTION	C14
INPUT CORD LENGTH	8 ft
INPUT NOMINAL VOLTAGE	208V default (200/208/220/230/240V)
INPUT FREQUENCY RANGE	60 Hz: 50–70 Hz, 50 Hz: 40–60 Hz
INPUT POWER FACTOR	>.99
RECEPTACLE	(8) C13
NUMBER OF OUTPUTS C13	8
OUTPUT WAVEFORM	True sine wave
VOLTAGE	208 V
OUTPUT NOMINAL VOLTAGE	208V default (200/208/220/230/240/250V)
FEED TYPE	1
RUNTIME GRAPH	\$row.attributeValue.cdata
BATTERY MANAGEMENT	ABM technology (3-stage charging extends battery service life by 50% and provides advance warning for battery replacement)
BATTERY REPLACEMENT	Hot-swappable internal batteries and extended battery modules (EBMs)
EXTENDED BATTERY CAPABILITY	Yes
STANDARD FACTORY WARRANTY	• 3-YEAR FACTORY WARRANTY • - 3 years • - Parts, electronics

	- and batteries coverage - Standard ground shipping - Technical support
EXTENDED SERVICE PLANS	• ADVANCED DEPOT EXCHANGE • - 5-year depot repair: 9SW5Y-1500UC • - Expedited parts coverage for 5 years • - Parts, electronics and UPS batteries coverage • - Next business day shipping • - Technical support • • 5-YEAR ON-SITE PLAN: WFLN75XX-2509UC • - On-site parts and labor coverage for years 5 • - Parts, electronics and UPS batteries coverage • - 24x7 on-site labor coverage, next-day response • - Next-day shipping • - Technical support
COMMUNICATION	• (1) MiniSlot • (1) USB port • (1) Serial RS-232 port • (1) RPO/ROO/Signal input terminal • (1) mini-terminal block for output relay
EXPANSION SLOTS	• (1) Mini-Slot (MS) expansion port. Optional connectivity cards may be ordered separately. • - Gigabit Web/SNMP card part number: NETWORK-M3 • - Modbus card part number: INDGW-M2 • - Relay card part number: RELAY-MS

USER INTERFACE	5-button graphical user interface
POTENTIAL FREE SWITCH CONTACT	Yes
ALTITUDE	3000 m
BTU RATING	Online : 424 BTU/hr, Battery : 767 BTU/hr, High efficiency : 151 BTU/hr
NOISE LEVEL	51 dB at 1m
RELATIVE HUMIDITY	0-96% non-condensing
TEMPERATURE RANGE	0° to 40°C (32° to 104°F)
MOUNTING METHOD	Vertical
EFFICIENCY AT MAX. LOAD	92.4%
MAX NUMBER OF BATTERY PACKS	4
OUTPUT FREQUENCY	50/60 Hz
OUTPUT POWER FACTOR	0.9
