



□□□□□

Eaton 9SX3000HW

Eaton 9SX online, extended runtime UPS, 3000 VA, 2700 W, Hardwired input/output, 13.6"Hx8.4"Wx16.2"D, 77.2 lb., network card optional

□□□□

PRODUCT NAME	Eaton 9SX UPS
CATALOG NUMBER	9SX3000HW
UPC	743172091277
PRODUCT LENGTH/DEPTH	16.2 in
PRODUCT HEIGHT	13.6 in
PRODUCT WIDTH	8.4 in
PRODUCT WEIGHT	77.2 lb
COMPLIANCES	FCC Compliant CE Marked
CERTIFICATIONS	cULus Listed



Powering Business Worldwide

□□□□	
TOPOLOGY	Online/Double-conversion
RACK SIZE	0U
CONSTRUCTION TYPE	Free standing model
COLOR	Black
VA RATING	3000 VA
WATTAGE	2700 W
PACKAGE CONTENTS	• 9SX3000HW Eaton 9SX Double-Conversion UPS • USB cable • RS-232 cable • Quick start guide
INTERNAL BYPASS	Yes
INPUT CONNECTION	Hardwired
INPUT NOMINAL VOLTAGE	120V default (100/110/120/125V)
INPUT FREQUENCY RANGE	60 Hz: 50–70 Hz, 50 Hz: 40–60 Hz
INPUT POWER FACTOR	>.99
RECEPTACLE	Hardwired
NUMBER OF OUTPUTS HARDWIRED	1
OUTPUT WAVEFORM	True sine wave
VOLTAGE	120V
OUTPUT NOMINAL VOLTAGE	120V default (100/110/120/125V)
FEED TYPE	1
RUNTIME GRAPH	\$row.attributeValue.cdata
BATTERY MANAGEMENT	ABM technology (3-stage charging extends battery service life by 50% and provides advance warning for battery replacement)
BATTERY REPLACEMENT	Hot-swappable internal batteries and extended battery modules (EBMs)
EXTENDED BATTERY CAPABILITY	Yes
STANDARD FACTORY WARRANTY	• 3-YEAR FACTORY WARRANTY • - 3 years • - Parts, electronics and batteries coverage • - Standard ground shipping

-
- - Technical support

EXTENDED SERVICE PLANS

- ADVANCED DEPOT EXCHANGE
- - 5-year depot repair: 9SW5Y-3000UC
- - Expedited parts coverage for 5 years
- - Parts, electronics and UPS batteries coverage
- - Next business day shipping
- - Technical support
-
- 5-YEAR ON-SITE PLAN: WFLN75XX-6009UC
- - On-site parts and labor coverage for years 5
- - Parts, electronics and UPS batteries coverage
- - 24x7 on-site labor coverage, next-day response
- - Next-day shipping
- - Technical support

COMMUNICATION

- (1) MiniSlot
- (1) USB port
- (1) Serial RS-232 port
- (1) RPO/ROO/Signal input terminal
- (1) mini-terminal block for output relay

EXPANSION SLOTS

- (1) Mini-Slot (MS) expansion port. Optional connectivity cards may be ordered separately.
- - Gigabit Web/SNMP card part number: NETWORK-M3
- - Modbus card part number: MODBUS-MS
- - Relay card part

number: RELAY-MS	
USER INTERFACE	5-button graphical user interface
POTENTIAL FREE SWITCH CONTACT	Yes
ALTITUDE	3000 m
BTU RATING	Online : 1020 BTU/hr, Battery : 1340 BTU/hr, High efficiency : 350 BTU/hr
NOISE LEVEL	<53 dB at 1 meter
RELATIVE HUMIDITY	0-96% non-condensing
TEMPERATURE RANGE	0° to 40°C (32° to 104°F)
MOUNTING METHOD	Vertical
MAX NUMBER OF BATTERY PACKS	4
OUTPUT FREQUENCY	50/60 Hz
OUTPUT POWER FACTOR	0.9
