



## Eaton 9SX700I-AU

Eaton 9SX UPS, AU, Tower, 700VA, 630W, 240VAC, Input: IEC C14, Output: AUS 10A x 4, built-in battery, Multilingual graphical LCD display

□□□□

<b>PRODUCT NAME</b>	Eaton 9SX UPS
<b>CATALOG NUMBER</b>	9SX700I-AU
<b>PRODUCT LENGTH/DEPTH</b>	160 mm
<b>PRODUCT HEIGHT</b>	252 mm
<b>PRODUCT WIDTH</b>	357 mm
<b>PRODUCT WEIGHT</b>	11.5 kg
<b>COMPLIANCES</b>	CB CE Marked RCM
<b>CERTIFICATIONS</b>	IEC 61000-4 EN 62040-3 IEC/EN 62040-1 IEC/EN 62040-2



Powering Business Worldwide

<b>TOPOLOGY</b>	Online/Double-conversion
<b>CONSTRUCTION TYPE</b>	Free standing model
<b>COLOR</b>	Black
<b>VA RATING</b>	700 VA
<b>WATTAGE</b>	630 W
<b>INTERNAL BYPASS</b>	Yes
<b>HOT SWAP POWER</b>	No
<b>AUTO SHUTDOWN FUNCTION</b>	Yes
<b>INPUT NOMINAL VOLTAGE</b>	240V
<b>NOMINAL FREQUENCY</b>	50/60 Hz
<b>INPUT FREQUENCY RANGE</b>	40-70 Hz
<b>RECEPTACLE</b>	AUS 10A x 4
<b>OUTPUT WAVEFORM</b>	Sine wave
<b>VOLTAGE</b>	240V
<b>OUTPUT NOMINAL VOLTAGE</b>	240V
<b>VOLTAGE TYPE</b>	AC
<b>RUNTIME GRAPH</b>	View runtime graph
<b>BATTERY REPLACEMENT</b>	Hot swappable
<b>BATTERY TYPE</b>	Sealed, lead-acid
<b>EXTENDED BATTERY CAPABILITY</b>	Yes
<b>EXPANSION SLOTS</b>	One slot for optional communication card
<b>INCLUDES NETWORK CARD</b>	No
<b>SOFTWARE COMPATIBILITY</b>	Eaton Intelligent Power Manager, Eaton Intelligent Power Protector
<b>USER INTERFACE</b>	Multilingual graphical LCD display
<b>ALTITUDE</b>	<1000m for nominal power, 10% power degrading every 1000m (up to 3000m)
<b>NOISE LEVEL</b>	<40 dB at 1 meter
<b>RELATIVE HUMIDITY</b>	0-96% non-condensing
<b>TEMPERATURE RANGE</b>	0° to 40°C (32° to 104°F)
<b>INPUT VOLTAGE RANGE</b>	190-276 Vac without derating (up to 120-276 Vac with derating)
<b>OUTPUT FREQUENCY</b>	50/60 Hz

