



Eaton AC10

Eaton Bussmann series low voltage british standard fuse, 10A, AC 550 V, 21 x 114 mm, gL/gG

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	AC10
UPC	051712844734
PRODUCT LENGTH/DEPTH	113 mm
PRODUCT HEIGHT	21 mm
PRODUCT WIDTH	21 mm
PRODUCT WEIGHT	60.4 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	BS88 IEC 60269 EAC

□□□□

AMPERAGE RATING	10 A
FITTED WITH:	Centre bolted tags
CURRENT TYPE	AC/DC
MOUNTING DIMENSION	M6
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	97.5 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
RATED VOLTAGE AC	550 V
RATED VOLTAGE DC	250 V
CLASS	Class gG/gL
FUSE TYPE	AC
UTILIZATION CATEGORY	gG (cable protection/equipment protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	2.4 W
CONNECTION	97 mm fixing centre
CONSTRUCTION	BS88
CONSTRUCTION SIZE	Other
FUSE SHAPE	Center bolted tags
VOLTAGE TYPE	AC/DC
VOLTAGE RATING	550 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

□□

DECLARATIONS OF
CONFORMITY

[eaton-low-voltage-british-
standard-fuse-declaration-
of-conformity-
uk250945en.pdf](#)

