


Eaton AC20

Eaton Bussmann series low voltage british standard fuse, 20A, AC 550 V, 21 x 114 mm, gL/gG

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	AC20
UPC	051712844758
PRODUCT LENGTH/DEPTH	114 mm
PRODUCT HEIGHT	21 mm
PRODUCT WIDTH	21 mm
PRODUCT WEIGHT	60.4 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	BS88 IEC 60269 EAC

AMPERAGE RATING	20 A
FITTED WITH:	Centre bolted tags
CURRENT TYPE	AC/DC
MOUNTING DIMENSION	M6
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	97.5 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
RATED VOLTAGE AC	550 V
RATED VOLTAGE DC	250 V
CLASS	Class gG/gL
FUSE TYPE	AC
UTILIZATION CATEGORY	gG (cable protection/equipment protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	3.1 W
CONNECTION	97 mm fixing centre
CONSTRUCTION	BS88
CONSTRUCTION SIZE	Other
FUSE SHAPE	Center bolted tags
VOLTAGE TYPE	AC AC/DC
VOLTAGE RATING	550 Vac, 250 Vdc
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

