



□□□□□

## Eaton AC25

Eaton Bussmann series low voltage british standard fuse, 25A, AC 500 V, 21 x 114 mm, gL/gG

□□□□

|                                 |                                                               |
|---------------------------------|---------------------------------------------------------------|
| <b>PRODUCT NAME</b>             | Eaton Bussmann series<br>low voltage british<br>standard fuse |
| <b>CATALOG NUMBER</b>           | AC25                                                          |
| <b>UPC</b>                      | 051712844765                                                  |
| <b>PRODUCT<br/>LENGTH/DEPTH</b> | 114 mm                                                        |
| <b>PRODUCT HEIGHT</b>           | 21 mm                                                         |
| <b>PRODUCT WIDTH</b>            | 21 mm                                                         |
| <b>PRODUCT WEIGHT</b>           | 60.4 g                                                        |
| <b>COMPLIANCES</b>              | CE Marked<br>RoHS Compliant                                   |
| <b>CERTIFICATIONS</b>           | BS88<br>IEC 60269<br>EAC                                      |

□□□□

|                                                |                                                  |
|------------------------------------------------|--------------------------------------------------|
| AMPERAGE RATING                                | 25 A                                             |
| FITTED WITH:                                   | Centre bolted tags                               |
| CURRENT TYPE                                   | AC/DC                                            |
| MOUNTING DIMENSION                             | M6                                               |
| CENTER-TO-CENTER<br>DISTANCE OF<br>CONNECTIONS | 97.5 mm                                          |
| BREAKING CAPACITY                              | 80 kA                                            |
| RATED SWITCHING<br>CAPACITY                    | 80 kA                                            |
| RATED VOLTAGE AC                               | 500 V                                            |
| RATED VOLTAGE DC                               | 250 V                                            |
| CLASS                                          | Class gG/gL                                      |
| FUSE TYPE                                      | AC                                               |
| UTILIZATION CATEGORY                           | gG (cable<br>protection/equipment<br>protection) |
| COLOR                                          | None                                             |
| INTERRUPT RATING                               | 80 kAIC                                          |
| FUSE INDICATOR                                 | None                                             |
| INSULATED METAL<br>GRIPPING LUGS (IMGL)        | No                                               |
| WATT LOSSES                                    | 3.2 W                                            |
| CONNECTION                                     | 97 mm fixing centre                              |
| CONSTRUCTION                                   | BS88                                             |
| CONSTRUCTION SIZE                              | Other                                            |
| FUSE SHAPE                                     | Center bolted tags                               |
| VOLTAGE TYPE                                   | AC<br>AC/DC                                      |
| VOLTAGE RATING                                 | 500 Vac, 250 Vdc                                 |
| TYPE                                           | Fuse                                             |
| APPLICATION                                    | general industrial<br>applications               |
| FUSE SYSTEM<br>(ACCORDING TO IEC<br>60269)     | Other                                            |

□□

DECLARATIONS OF  
CONFORMITY

[eaton-low-voltage-british-  
standard-fuse-declaration-  
of-conformity-  
uk250945en.pdf](#)

|                 |
|-----------------|
| PROJECT NAME:   |
| PROJECT NUMBER: |
| PREPARED BY:    |
|                 |



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025   

Follow us on social media to get the latest product and support information.

