

## Eaton AD25

Eaton Bussmann series low voltage British standard fuse, 25 A, 500 V, 80 kAIC, 3.2 Watt, 111 mm fixing centre

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	AD25
UPC	051712838511
PRODUCT LENGTH/DEPTH	129 mm
PRODUCT HEIGHT	21 mm
PRODUCT WIDTH	22 mm
PRODUCT WEIGHT	66.9 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	BS88 IEC 60269 EAC

<b>AMPERAGE RATING</b>	25 A
<b>FITTED WITH:</b>	Centre bolted tags
<b>CURRENT TYPE</b>	AC/DC
<b>MOUNTING DIMENSION</b>	M8
<b>CENTER-TO-CENTER DISTANCE OF CONNECTIONS</b>	111 mm
<b>BREAKING CAPACITY</b>	80 kA
<b>RATED SWITCHING CAPACITY</b>	80 kA
<b>RATED VOLTAGE AC</b>	500 V
<b>RATED VOLTAGE DC</b>	250 V
<b>CLASS</b>	Class gG/gL
<b>FUSE TYPE</b>	AD
<b>UTILIZATION CATEGORY</b>	gG (cable protection/equipment protection)
<b>COLOR</b>	None
<b>INTERRUPT RATING</b>	80 kAIC
<b>FUSE INDICATOR</b>	None
<b>INSULATED METAL GRIPPING LUGS (IMGL)</b>	No
<b>WATT LOSSES</b>	3.2 W
<b>CONNECTION</b>	111 mm fixing centre
<b>CONSTRUCTION</b>	BS88
<b>CONSTRUCTION SIZE</b>	Other
<b>FUSE SHAPE</b>	Center bolted tags
<b>VOLTAGE TYPE</b>	AC AC/DC
<b>VOLTAGE RATING</b>	500 V
<b>TYPE</b>	Fuse
<b>APPLICATION</b>	general industrial applications
<b>FUSE SYSTEM (ACCORDING TO IEC 60269)</b>	Other

## DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-  
standard-fuse-declaration-  
of-conformity-  
uk250945en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

