



## Eaton AH563C6W

Eaton Arrow Hart pin and sleeve connector, IP69K Rated, #8 - #2 AWG, #10 - #2 AWG (Ground), #12 - #16 AWG (Pilot), 63A, 220/380V - 240/415V, Back wire, Red, Nickel plated brass, IP67, Nylon, 4-pole, 5-wire, 0.66-1.5in (1.68-3.81cm), Female



<b>PRODUCT NAME</b>	Eaton Arrow Hart pin and sleeve connector
<b>CATALOG NUMBER</b>	AH563C6W
<b>UPC</b>	040893624280
<b>PRODUCT LENGTH/DEPTH</b>	11.5 in
<b>PRODUCT HEIGHT</b>	5.125 in
<b>PRODUCT WIDTH</b>	5.125 in
<b>PRODUCT WEIGHT</b>	2.246 lb
<b>CERTIFICATIONS</b>	UL Listed cRUus



Powering Business Worldwide

