

Eaton AM5F2MG070M

Eaton Crouse-Hinds series LynxPOWER Micro-Mini cordset, 4A, #22 AWG, Female, 90° plug, internal thread, pigtail, Passive, Dual key, Zinc, Five-pole, AC, 300 Vac, 7 m cable length

PRODUCT NAME	Eaton Crouse-Hinds series LynxPOWER Micro-Mini cordset
CATALOG NUMBER	AM5F2MG070M
UPC	662275377258
PRODUCT LENGTH/DEPTH	1.7 in
PRODUCT HEIGHT	1.17 in
PRODUCT WIDTH	0.64 in
PRODUCT WEIGHT	0.56 lb

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	IEC NEC/CEC
NEMA RATING	13 6P 4 1 3
INGRESS PROTECTION (IP) RATINGS	IP68
TYPE	AC
AMPERAGE RATING	4 A
VOLTAGE RATING	300 Vac
NUMBER OF POLES	Five-pole
CABLE/WIRE SIZE	#22 AWG
CABLE LENGTH	7 m
CONNECTOR TYPE	Passive
GENDER	Female
KEY TYPE	Dual key
MATERIAL	Zinc
CONFIGURATION	Female, 90° plug, internal thread, pigtail

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

[Eaton Specification Sheet - AM5F2MG070M](#)

[LynxPower industrial connectivity solutions](#)

[Mini-Line and Micro-Mini Cordsets, Receptacles and Multi-port Boxes catalog page](#)

Follow us on social media to get the latest product and support information.

