



Eaton AN16KN0A

Eaton Freedom NEMA Starter, Full voltage non-reversing, C306 bi-metal overload relay, NEMA Size 3 open enclosure - 90 A, Horizontal mounting, 120/60 or 110/50 coil voltage

□□□□

PRODUCT NAME	Eaton Freedom NEMA motor control starter
CATALOG NUMBER	AN16KN0A
UPC	782113603896
PRODUCT LENGTH/DEPTH	5.94 in
PRODUCT HEIGHT	11.35 in
PRODUCT WIDTH	4.08 in
PRODUCT WEIGHT	11 lb
CERTIFICATIONS	CSA Certified UL Listed
CATALOG NOTES	Heater Packs must be purchased separately

□□□□	
NEMA FRAME SIZE	NEMA Size 3
RELAY	C306 bi-metal
TYPE	Starter
SPECIAL FEATURES	Starter w/C306 bi-metal OLR
CONFIGURATION	Non-reversing
PHASE	Three-phase
AMPERAGE RATING	90 A
SIZE	3
HORSEPOWER	25 hp at 208 V, 30 hp at 240 V, 50 hp at 480/600 V
MOUNTING	Horizontal
OVERLOAD RELAY	C306 bi-metal
COIL VOLTAGE	120/60 or 110/50

□□

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
□□:



□□□□
Eaton House
30 Pembroke Road
Dublin 4, □□□
Eaton.com

© 2025 □□ □□□□□□

Follow us on social media to get the latest product and support information.

