



□□□□

Eaton APS22270L

Eaton's Crouse-Hinds series Pauluhn AllPro APS linear fluorescent light fixture, 3/4" entry, 50/60 Hz, 2 ft lamp, Fluorescent, Flat, Polycarbonate lens, CF 2G11, 304 stainless steel, 2-lamp, Lamps included, Standard wall/ceiling, 120-277 Vac, 40W

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series Pauluhn AllPro APS linear fluorescent light fixture
CATALOG NUMBER	APS22270L
UPC	662276613256
PRODUCT LENGTH/DEPTH	31.5 in
PRODUCT HEIGHT	6 in
PRODUCT WIDTH	9.75 in
PRODUCT WEIGHT	21 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION Hazardous/Classified Locations

STANDARDS TYPE NEC/CEC

NEC HAZARDOUS RATING Class I, Division 2
Class II, Division 1
Class III

NEMA RATING 4X

INGRESS PROTECTION (IP) RATINGS IP66

Product specifications

LAMP TYPE Fluorescent

LENS TYPE Flat

MATERIAL 304 stainless steel

LAMP LENGTH 2 ft

NUMBER OF LAMPS 2-lamp

LIGHT TYPE CF 2G11

VOLTAGE RATING 120-277 Vac

FREQUENCY RATING 50/60 Hz

MOUNTING Standard wall/ceiling

ENTRY SIZE 3/4"

WATTAGE 40W

LENS MATERIAL Polycarbonate

SPECIAL FEATURES Lamps included

□□

[IF LBL1518 - Pauluhn AllPro Linear Fluorescent - Flat Lens, Compact Fixture](#)

□□□□□

[IF LBL1516 - Pauluhn AllPro Linear Fluorescent - Flat Lens](#)

□□□□□□□

[Eaton Specification Sheet - APS22270L](#)

□□□□

[Crouse-Hinds series Pauluhn AllPro Hazardous Area Linear Fluorescent brochure](#)

□□□□

[Crouse-Hinds series Pauluhn AllPro Hazardous Area Linear Fluorescent catalog page](#)

