

Eaton APS42170WZ 125VDC

Eaton Crouse-Hinds series Pauluhn AllPro APS linear fluorescent light fixture,3/4" entry,50/60 Hz,4 ft lamp,Flat,Polycarbonate lens,T8 bi-pin,316 stainless steel,2-lamp,Dual safety cable attachment points,Standard wall/ceiling,125 Vdc,32W

PRODUCT NAME	Eaton Crouse-Hinds series Pauluhn AllPro APS linear fluorescent light fixture
CATALOG NUMBER	APS42170WZ 125VDC
UPC	662276611238
PRODUCT LENGTH/DEPTH	55.5 in
PRODUCT HEIGHT	6 in
PRODUCT WIDTH	9.75 in
PRODUCT WEIGHT	29.3 lb

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 2 Class II, Division 1 Class III
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

Product specifications

LAMP TYPE	Fluorescent
LENS TYPE	Flat
MATERIAL	316 stainless steel
LAMP LENGTH	4 ft
NUMBER OF LAMPS	2-lamp
LIGHT TYPE	T8 bi-pin
VOLTAGE RATING	125 Vdc
FREQUENCY RATING	50/60 Hz
MOUNTING	Standard wall/ceiling
ENTRY SIZE	3/4"
WATTAGE	32W
LENS MATERIAL	Polycarbonate
SPECIAL FEATURES	Dual safety cable attachment points

[IF LBL1516 - Pauluhn AllPro Linear Fluorescent - Flat Lens](#)

[IF LBL1518 - Pauluhn AllPro Linear Fluorescent - Flat Lens, Compact Fixture](#)

[Eaton Specification Sheet - APS42170WZ 125VDC](#)

[Crouse-Hinds series Pauluhn AllPro Hazardous Area Linear Fluorescent brochure](#)

[Crouse-Hinds series Pauluhn AllPro Hazardous Area Linear Fluorescent catalog page](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

