



□□□□□

Eaton APS43170EM1WZ

Eaton Crouse-Hinds series Pauluhn AllPro APS linear fluorescent,3/4" entry,4 ft,Flat,Polycarb lens,T8 bi-pin,316 SS,3-lamp,battery back-up,one lamp,277V maximum,dual safety cable attachment points,Standard wall/ceiling,120-277 Vac,32W

□□□□□

PRODUCT NAME	Eaton Crouse-Hinds series Pauluhn AllPro APS linear fluorescent light fixture
CATALOG NUMBER	APS43170EM1WZ
UPC	662276520677
PRODUCT LENGTH/DEPTH	55.5 in
PRODUCT HEIGHT	6 in
PRODUCT WIDTH	9.75 in
PRODUCT WEIGHT	37 lb

Certifications and compliances	
AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 2 Class II, Division 1 Class III
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

Product specifications	
LAMP TYPE	Fluorescent
LENS TYPE	Flat
MATERIAL	316 stainless steel
LAMP LENGTH	4 ft
NUMBER OF LAMPS	3-lamp
LIGHT TYPE	T8 bi-pin
VOLTAGE RATING	120-277 Vac
FREQUENCY RATING	50/60 Hz
MOUNTING	Standard wall/ceiling
ENTRY SIZE	3/4"
WATTAGE	32W
LENS MATERIAL	Polycarbonate
SPECIAL FEATURES	Emergency battery back-up ballast, one lamp, 277V maximum, dual safety cable attachment points

Links	
□□	IF LBL1516 - Pauluhn AllPro Linear Fluorescent - Flat Lens
□□□□□	IF LBL1518 - Pauluhn AllPro Linear Fluorescent - Flat Lens, Compact Fixture
□□□□□□□	Eaton Specification Sheet - APS43170EM1WZ
□□□□	Crouse-Hinds series Pauluhn AllPro Hazardous Area Linear Fluorescent brochure
□□□□	Crouse-Hinds series Pauluhn AllPro Hazardous Area Linear Fluorescent catalog page

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

