

Eaton ARS22270

Eaton Crouse-Hinds series Pauluhn AllPro ARS linear fluorescent light fixture,3/4" entry,50/60 Hz,2 ft lamp,Flat,Polycarbonate lens,CF 2G11,304 stainless steel,2-lamp,Standard wall/ceiling,120-277 Vac,40W

PRODUCT NAME	Eaton Crouse-Hinds series Pauluhn AllPro ARS linear fluorescent light fixture
CATALOG NUMBER	ARS22270
UPC	662276389236
PRODUCT LENGTH/DEPTH	31.5 in
PRODUCT HEIGHT	6 in
PRODUCT WIDTH	9.75 in
PRODUCT WEIGHT	21 lb

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

Product specifications

LAMP TYPE	Fluorescent
LENS TYPE	Flat
LAMP LENGTH	2 ft
NUMBER OF LAMPS	2-lamp
LIGHT TYPE	CF 2G11
VOLTAGE RATING	120-277 Vac
FREQUENCY RATING	50/60 Hz
ENTRY SIZE	3/4"
WATTAGE	40W
MATERIAL	304 stainless steel
LENS MATERIAL	Polycarbonate

[IF LBL1518 - Pauluhn
AllPro Linear Fluorescent -
Flat Lens, Compact Fixture](#)

[IF LBL1516 - Pauluhn
AllPro Linear Fluorescent -
Flat Lens](#)

[Eaton Specification Sheet -
ARS22270](#)

[Crouse-Hinds series
Pauluhn AllPro Industrial
Linear Fluorescent catalog
page](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

