




Eaton B110-SP-DP

In-Line DisplayPort Surge Protector - 4K 60 Hz, HDCP, IEC Compliant, TAA

□□□□

PRODUCT NAME	Eaton Tripp Lite series surge protector
CATALOG NUMBER	B110-SP-DP
UPC	037332295187
PRODUCT LENGTH/DEPTH	0.61 in
PRODUCT HEIGHT	1.83 in
PRODUCT WIDTH	0.88 in
PRODUCT WEIGHT	0.11 lb
COMPLIANCES	FCC Class B RoHS TAA Compliant
CERTIFICATIONS	EN 55032 CISPR 35/EN 55035 ICES IEC 61000

Specifications	
EFT PROTECTION	+/- 2kV (5 kHz/100kHz)
ESD PROTECTION	+/-15kV (AIR); +/-8kV (CONTACT)
LIGHTNING PROTECTION	1kV 1,2/50 (8/20µs)
RELATIVE HUMIDITY	0% to 85% RH, Non-Condensing
OPERATING TEMPERATURE	0° to 40°C
SURGE STYLE	IL - IN-LINE
TECHNOLOGY	DisplayPort
OPERATING TEMPERATURE RANGE	32° to 104°F (0° to 40°C)
STORAGE TEMPERATURE RANGE	5° to 122°F (-15° to 50°C)
CORD LENGTH	1 Foot
HOUSING COLOR	Black
MATERIAL	ABS
PRODUCT CATEGORY	In-Line Surge Protector
COLOR	Black
PACKAGE CONTENTS	B110-SP-DP In-Line DisplayPort Surge Protector Installation Instructions Grounding wire screw Grounding wire, 1 ft. (0.3 m)
PRODUCT FEATURES	TAA Compliant
PRODUCT HIGHLIGHTS	Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases Plug-and-play operation with no software required for easy, immediate installation Easy to connect between DP source and display using standard DP cabling Rapid reaction time under 1 ns helps prevent damage from power surges 2-year limited warranty (Worldwide) Supports UHD resolutions up to 4K @ 60 Hz for heightened video quality
PACKAGING TYPE	Box
PLUG COLOR	White
SIDE A CONNECTOR1	DISPLAYPORT (FEMALE)



SIDEB CONNECTOR1	DISPLAYPORT (MALE)
AC SUPPRESSION JOULE RATING	0
NUMBER OF PORTS	1
SIGNAL RANGE	15 ft
AC SUPPRESSION RESPONSE TIME	<1 NS
CONNECTOR PLATING	Gold
HDCP SPECIFICATION	2.2
MAX SUPPORTED VIDEO RESOLUTION	4K 60HZ
TAA COMPLIANCE	Yes
TOTAL OUTLETS	1
